

# CR2477N


3V Lithium Battery  
Swiss Made

## Technical Data Sheet

### Specifications


|                              |                       |
|------------------------------|-----------------------|
| Chemical System              | Li / MnO <sub>2</sub> |
| Nominal Voltage              | 3 V                   |
| Rated Capacity               | 950 mAh               |
| Standard Discharge Current   | 1.0 mA                |
| Max. Cont. Discharge Current | 2.5 mA                |
| Average Weight               | 8.3 g                 |
| Operating Temperature*       | -40 - +85 °C          |
| Self Discharge at 23 °C      | < 1% / year           |

### Dimensions




### Performance


Discharge performance at 23 °C




Discharge performance at 23 °C



Temperature performance Load 4.7kΩ



Cell capacity at various loads



\*In applications where the battery is exposed to temperatures above 70 °C, please contact Renata for consultancy.

Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative.

Rev. CR2477N. 06 / 12.06