









LOC	DIST	REVISIONS					
HM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
00071			H	REVISED PER ECO-14-011190	29JUL2014	GG	LS



1. MATERIAL: HOUSING - 94V-0 RATED POLYCARBONATE CLEAR
TERMINAL - 0.36 [0.014] THICK PHOSPHOR BRONZE PLATED WITH .178 μm [0.000007] THICK GOLD IN LOCALIZED AREA, OVER .762 μm [0.000030] THICK PALLADIUM NICKEL IN LOCALIZED PLATE AREA OVER 2.54 μm [0.000100] THICK NICKEL ON ENTIRE CONTACT.
WIRE HOLDER - POLYCARBONATE CLEAR.
SHIELD - COPPER ALLOY WITH 1.27 μm [0.000050] MINIMUM SEMI-BRIGHT (SATIN) NICKEL.
2. DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
3. PLUG WILL ACCEPT A 23-24 AWG SOLID CONDUCTOR, PROVIDED THE INSULATION CONDUCTOR DIAMETER IS WITHIN .89 - 1.09 [0.035 - .043]; WITH THE SUM OF DIAMETERS FOR ALL EIGHT CONDUCTORS WITHIN THE CABLE MUST NOT EXCEED 7.8MM [0.31 IN]. CABLE JACKET DIAMETER OF 6.0 - 7.0 MM [0.24 - .28 IN].
4. TERMINATED DIMENSION 6.15 [0.242] MAXIMUM.
5. PACKAGE 1,000 ASSEMBLIES, 1,000 WIRE HOLDERS, AND 1,000 SHIELDS.
6. PACKAGE 100 ASSEMBLIES, 100 WIRE HOLDERS, AND 100 SHIELDS.
8. PACKAGE 500 ASSEMBLIES, 500 WIRE HOLDERS, AND 500 SHIELDS.
10. UL RECOGNIZED: FILE NUMBER E81956.



6	5-1479185-3
8	5-1479185-2
5	5-1479185-1
PACKAGE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. GARRETT 24JAN02	TE Connectivity	
DIMENSIONS: MME[INCHES]		CHK M. DELPHIAS 24JAN02		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. DELPHIAS 24JAN02	NAME	
0 PLC ±		PRODUCT SPEC	KIT, 8 POSITION, MODULAR PLUG, SOLID WIRE, CATEGORY 6	
1 PLC ±		APPLICATION SPEC		
2 PLC ±		114-13035	SIZE	CAGE CODE
3 PLC ±		WEIGHT	100779	DRAWING NO
4 PLC ±		Customer Drawing	1479185	RESTRICTED TO
ANGLES		SCALE	8:1	SHEET
FINISH		REV	H	OF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-1479185-1](#)