


Diffuse sensors with background suppression

FHDK 04

sample drawing



* emitter axis

general data

type	background suppression
light source	pulsed point source LED
alignment / soiled lens indicator	flashing light indicator
light indicator	LED yellow
wave length	660 nm
beam diameter	2 mm
suppression of reciprocal influence	yes

electrical data

response time / release time	< 0,5 ms
voltage supply range +Vs	11 ... 30 VDC
current consumption max. (no load)	30 mA
current consumption typ.	20 mA
voltage drop Vd	< 2 VDC
output circuit	push-pull
output current	< 50 mA
short circuit protection	yes
reverse polarity protection	yes, supply only

mechanical data

width / diameter	4 mm
height / length	44,8 mm
depth	6,2 mm
type	rectangular
housing material	plastic (ASA)
front (optics)	PMMA

ambient conditions

operating temperature	-10 ... +50 °C
protection class	IP 65

sample picture



Diffuse sensors with background suppression

FHDK 04

order reference	sensing distance Tw	connection types	output function
FHDK 04G6101	30 mm $\pm$ 2 mm	cable 3 pin, 2 m	light operate
FHDK 04G6101/KS35A	30 mm $\pm$ 2 mm	flylead connector M8 4 pin, L=200 mm	light operate
FHDK 04G6102	50 mm $\pm$ 3 mm	cable 3 pin, 2 m	light operate
FHDK 04G6102/KS35A	50 mm $\pm$ 3 mm	flylead connector M8 4 pin, L=200 mm	light operate
FHDK 04G6111	30 mm $\pm$ 2 mm	cable 3 pin, 2 m	dark operate
FHDK 04G6111/KS35A	30 mm $\pm$ 2 mm	flylead connector M8 4 pin, L=200 mm	dark operate
FHDK 04G6112	50 mm $\pm$ 3 mm	cable 3 pin, 2 m	dark operate
FHDK 04G6112/KS35A	50 mm $\pm$ 3 mm	flylead connector M8 4 pin, L=200 mm	dark operate