



## 3" Core Wire & Cable Labels:

### B-499 Nylon Cloth Labels

Color: White Finish: Matte

Permanent adhesive allows labeling in environments with heat, cold, oil and dirt. Ideal for wire and cable marking, electronic component marking, laboratory vial identification, and general labeling.



| Diagram                                                                                                                                                                                                                                         | Part Number        | Material    | Color | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Horiz.Repeat C<br>Inch (mm) | Vert.Repeat D<br>Inch (mm) | Web Width E<br>Inch (mm) | Labels<br>Per Row | Labels<br>Per Pkg | Rec.<br>Ribbon |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|-------------|-------|----------------------------|-----------------------------|-----------------------------|----------------------------|--------------------------|-------------------|-------------------|----------------|
| Fig. 1                                                                                                                                                                                                                                          | THT-68-499-10      | Nylon Cloth | White | 0.500 (12.7)               | 0.750 (19.1)                | 0.600 (15.2)                | 0.850 (21.6)               | 2.500 (63.5)             | 4                 | 10,000            | R4900          |
| Fig. 1                                                                                                                                                                                                                                          | THT-162-499-10     | Nylon Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                | 1.562 (39.7)               | 3.700 (94.0)             | 4                 | 10,000            | R4904          |
| Fig. 1                                                                                                                                                                                                                                          | THT-165-499-5      | Nylon Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                | 1.562 (39.7)               | 3.700 (94.0)             | 4                 | 5,000             | R4904          |
| Fig. 1                                                                                                                                                                                                                                          | THT-69-499-3       | Nylon Cloth | White | 0.800 (20.3)               | 1.437 (36.5)                | 0.900 (22.9)                | 1.540 (39.1)               | 1.900 (48.3)             | 2                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-125-499-3      | Nylon Cloth | White | 0.900 (22.9)               | 0.500 (12.7)                | -                           | 0.600 (15.2)               | 1.100 (27.9)             | 1                 | 3,000             | R4902          |
| Fig. 1                                                                                                                                                                                                                                          | THT-152-499-3      | Nylon Cloth | White | 1.000 (25.4)               | 0.375 (9.5)                 | 1.075 (27.3)                | 0.475 (12.1)               | 2.300 (58.4)             | 2                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-136-499-3      | Nylon Cloth | White | 1.500 (38.1)               | 0.750 (19.1)                | -                           | 0.875 (22.2)               | 1.700 (43.2)             | 1                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-185-499-3      | Nylon Cloth | White | 1.750 (44.5)               | 1.000 (25.4)                | -                           | 1.125 (28.6)               | 1.950 (49.5)             | 1                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-186-499-3      | Nylon Cloth | White | 1.750 (44.5)               | 1.875 (47.6)                | -                           | 1.975 (50.2)               | 1.950 (49.5)             | 1                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-137-499-3      | Nylon Cloth | White | 2.000 (50.8)               | 1.000 (25.4)                | -                           | 1.125 (28.6)               | 2.200 (55.9)             | 1                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-151-499-3      | Nylon Cloth | White | 2.000 (50.8)               | 0.250 (6.4)                 | -                           | 0.350 (8.9)                | 2.200 (55.9)             | 1                 | 3,000             | R4902          |
| Fig. 2                                                                                                                                                                                                                                          | THT-19-499-1       | Nylon Cloth | White | 3.000 (76.2)               | 2.000 (50.8)                | -                           | 2.125 (54.0)               | 3.200 (81.3)             | 1                 | 1,000             | R4900          |
| <b>NOTICE BBP11 PRINTER ONLY:</b> The following part numbers ending with "-SC" are 1" Small Core Rolls specially designed for use in the BBP11 Printer and do not require the BBP11 media adaptor accessory. View page 68 for more information. |                    |             |       |                            |                             |                             |                            |                          |                   |                   |                |
| Fig. 2                                                                                                                                                                                                                                          | THT-125-499-1.5-SC | Nylon Cloth | White | 0.900 (22.9)               | 0.500 (12.7)                | -                           | 0.600 (15.2)               | 1.100 (27.9)             | 1                 | 1,500             | R4913          |
| Fig. 1                                                                                                                                                                                                                                          | THT-152-499-1.5-SC | Nylon Cloth | White | 1.000 (25.4)               | 0.375 (9.5)                 | 1.100 (27.9)                | 0.475 (12.0)               | 2.300 (58.4)             | 2                 | 1,500             | R4913          |
| Fig. 2                                                                                                                                                                                                                                          | THT-136-499-1.5-SC | Nylon Cloth | White | 1.500 (38.1)               | 0.750 (19.1)                | -                           | 0.875 (22.2)               | 1.100 (27.9)             | 1                 | 1,500             | R4913          |
| Fig. 2                                                                                                                                                                                                                                          | THT-151-499-1.5-SC | Nylon Cloth | White | 2.000 (50.8)               | 0.250 (6.4)                 | -                           | 0.350 (8.9)                | 2.200 (55.9)             | 1                 | 1,500             | R4913          |
| Fig. 2                                                                                                                                                                                                                                          | THT-137-499-1.5-SC | Nylon Cloth | White | 2.000 (50.8)               | 1.000 (25.4)                | -                           | 1.125 (28.6)               | 2.100 (53.3)             | 1                 | 1,500             | R4913          |

## 3" Core Wire & Cable Labels:

### B-508 Nomex® Wire and Cable Tags

Color: White, Yellow and Green Finish: Matte

Thermal transfer and dot matrix printable wire and cable bundle tag for harsh environments. Excellent tear, heat and solvent resistance. Meets the following industry specifications: SAE AS 81531, RoHS Compliant. Tested per ASTM E162, ASTM E662.




Figure 61



| Diagram | Part Number   | Material   | Color  | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Vert. Repeat D<br>Inch (mm) | Web Width E<br>Inch (mm) | Labels<br>Per Row | Labels<br>Per Pkg | Rec.<br>Ribbon |
|---------|---------------|------------|--------|----------------------------|-----------------------------|-----------------------------|--------------------------|-------------------|-------------------|----------------|
| Fig. 61 | HSNX-400-2-GR | Nomex® Tag | Green  | 2.200 (55.8)               | 0.410 (10.4)                | 0.622 (15.79)               | 3.250 (82.55)            | 1                 | 2,500             | R6002          |
| Fig. 61 | HSNX-400-2-WT | Nomex® Tag | White  | 2.200 (55.8)               | 0.410 (10.4)                | 0.622 (15.79)               | 3.250 (82.55)            | 1                 | 2,500             | R6002          |
| Fig. 61 | HSNX-400-2-YL | Nomex® Tag | Yellow | 2.200 (55.8)               | 0.410 (10.4)                | 0.622 (15.79)               | 3.250 (82.55)            | 1                 | 2,500             | R6002          |
| Fig. 61 | HSNX-800-2-GR | Nomex® Tag | Green  | 2.200 (55.8)               | 0.410 (10.4)                | 1.012 (25.70)               | 3.250 (82.55)            | 1                 | 2,500             | R6002          |
| Fig. 61 | HSNX-800-2-WT | Nomex® Tag | White  | 2.200 (55.8)               | 0.410 (10.4)                | 1.012 (25.70)               | 3.250 (82.55)            | 1                 | 2,500             | R6002          |
| Fig. 61 | HSNX-800-2-YL | Nomex® Tag | Yellow | 2.200 (55.8)               | 0.410 (10.4)                | 1.012 (25.70)               | 3.250 (82.55)            | 1                 | 2,500             | R6002          |

## 3" Core Wire & Cable Labels:

### B-7643 Heatex™ Cable Markers

Color: White Finish: Matte

Polyurethane tag material for dot matrix and thermal transfer printing. Low-halegen material that is Rohs compliant.

| Part Number        | Material     | Color  | Label Width A<br>Inch (mm) | Label Height B<br>Inch (mm) | Labels Per Row | Labels Per Pkg | Rec. Ribbon |
|--------------------|--------------|--------|----------------------------|-----------------------------|----------------|----------------|-------------|
| HSCM-2400-0.390-WT | Polyurethane | White  | 2.362 (60.0)               | 0.394 (10.0)                | 1              | 1,000          | R6002       |
| HSCM-2400-0.390-YL | Polyurethane | Yellow | 2.400 (61.0)               | 0.390 (9.0)                 | 1              | 1,000          | R6002       |
| HSCM-3000-0.500-WT | Polyurethane | White  | 2.953 (75.0)               | 0.394 (10.0)                | 1              | 1,000          | R6002       |
| HSCM-3000-0.500-YL | Polyurethane | Yellow | 2.953 (75.0)               | 0.394 (10.0)                | 1              | 1,000          | R6002       |
| HSCM-3000-0.625-WT | Polyurethane | White  | 2.953 (75.0)               | 0.591 (15.0)                | 1              | 1,000          | R6002       |
| HSCM-3000-0.625-YL | Polyurethane | Yellow | 2.953 (75.0)               | 0.591 (15.0)                | 1              | 1,000          | R6002       |
| HSCM-3000-1-WT     | Polyurethane | White  | 2.953 (75.0)               | 0.984 (25.0)                | 1              | 500            | R6002       |
| HSCM-3000-1-YL     | Polyurethane | Yellow | 2.953 (75.0)               | 0.984 (25.0)                | 1              | 500            | R6002       |