

## Voltage and Safety Marker Books



### Material Chart

| Material | Print Method | Temperature Range                 | Features                                                                                                               |
|----------|--------------|-----------------------------------|------------------------------------------------------------------------------------------------------------------------|
| Vinyl    | Pre-Printed  | -40°F to 200°F<br>(-40°C to 93°C) | Indoor rated; economical general purpose material; excellent adhesion properties when applied to a clean, dry surface. |

| Part Number | Legend | Markers Per Page | Markers Per Book | Std. Qty. Book(s) |
|-------------|--------|------------------|------------------|-------------------|
|-------------|--------|------------------|------------------|-------------------|


### Voltage Markers 1.50" x 3.25" (38.00mm x 82.00mm)

|               |               |   |    |   |
|---------------|---------------|---|----|---|
| PCVB-110Y     | 110 Volts     | 3 | 30 | 1 |
| PCVB-220Y     | 220 Volts     |   |    |   |
| PCVB-277Y     | 277 Volts     |   |    |   |
| PCVB-277/480Y | 277/480 Volts |   |    |   |
| PCVB-440Y     | 440 Volts     |   |    |   |
| PCVB-480Y     | 480 Volts     |   |    |   |
| PCVB-4160Y    | 4160 Volts    |   |    |   |

### Safety Markers 1.50" x 3.25" (38.00mm x 82.00mm)

|         |                     |   |    |   |
|---------|---------------------|---|----|---|
| PSSB-13 | Danger High Voltage | 3 | 30 | 1 |
|---------|---------------------|---|----|---|

## Hazard Tape




### Material Chart

| Material | Print Method | Temperature Range                 | Features                                                                                                                                               |
|----------|--------------|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Vinyl    | Pre-Printed  | -20°F to 175°F<br>(-29°C to 79°C) | Indoor rated; color-coded for quick identification; can be used in place of paint; excellent adhesion properties when applied to a clean, dry surface. |

| Part Number  | Part Description                                | Width |       | Length |      | Std. Pkg. Qty. | Std. Ctn. Qty. |
|--------------|-------------------------------------------------|-------|-------|--------|------|----------------|----------------|
|              |                                                 | In.   | mm    | Ft.    | m    |                |                |
| HT2S-BLK-YEL | Black/yellow stripe, adhesive continuous tape.  | 2.00  | 50.80 | 54.0   | 16.5 | 1              | 12             |
| HT2S-RED-WHT | Red/white striped, adhesive continuous tape.    | 2.00  | 50.80 | 54.0   | 16.5 | 1              | 12             |
| HT3S-BLK-YEL | Black/yellow striped, adhesive continuous tape. | 3.00  | 76.20 | 54.0   | 16.5 | 1              | 10             |
| HT3S-RED-WHT | Red/white striped, adhesive continuous tape.    | 3.00  | 76.20 | 54.0   | 16.5 | 1              | 10             |

## Solid Color Adhesive Warning Tape



### Material Chart

| Material | Temperature Range                 | Features                                                                                                                                               |
|----------|-----------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------|
| Vinyl    | -20°F to 175°F<br>(-29°C to 79°C) | Indoor rated; color-coded for quick identification; can be used in place of paint; excellent adhesion properties when applied to a clean, dry surface. |

| Part Number | Color  | Width |       | Length |      | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|--------|-------|-------|--------|------|----------------|----------------|
|             |        | In.   | mm    | Ft.    | m    |                |                |
| HT2-BLU     | Blue   | 2.00  | 50.80 | 180.0  | 55.0 | 1              | 5              |
| HT2-GRN     | Green  | 2.00  | 50.80 | 180.0  | 55.0 | 1              | 5              |
| HT2-ORN     | Orange | 2.00  | 50.80 | 180.0  | 55.0 | 1              | 5              |
| HT2-RED     | Red    | 2.00  | 50.80 | 180.0  | 55.0 | 1              | 5              |
| HT2-WHT     | White  | 2.00  | 50.80 | 180.0  | 55.0 | 1              | 5              |
| HT2-YEL     | Yellow | 2.00  | 50.80 | 180.0  | 55.0 | 1              | 5              |