



# Occupancy & Vacancy Sensors & Timers Wall Box Timers

125, 125-T, 250 & 277VAC, 60 Hz

Pass & Seymour




## Applications

- Lighting
- Whirlpools and spas
- Heating and heat lamps
- Exhaust fans
- Saunas
- Ventilating and air conditioning

## Features

- Units with "Hold" feature may be turned counter-clockwise to hold the load on without timing function.
- Turning clockwise causes unit to time load off after desired time delay.
- Quiet operation.
- Time range from 5 minutes to 12 hours.
- Available with or without hold.
- Decorator styling.
- Easily installed.
- Large head screw terminals.
- Accurate to  $\pm 5$  percent.
- Motor rated.
- Energy saving.



970151

| Catalog Number                                     | Description        | Time Range | Color                       |
|----------------------------------------------------|--------------------|------------|-----------------------------|
| <b>Specification Grade Decorator Rotary Timers</b> |                    |            |                             |
| 970151<br>97015W<br>97015LA                        | Timeout, No Hold   | 15 Minutes | Ivory White<br>Light Almond |
| 970301<br>97030W<br>97030LA                        | Timeout, No Hold   | 30 Minutes | Ivory White<br>Light Almond |
| 970601<br>97060W                                   | Timeout, No Hold   | 60 Minutes | Ivory White                 |
| 971151<br>97115W                                   | Timeout, With Hold | 15 Minutes | Ivory White                 |
| 971301<br>97130W                                   | Timeout, With Hold | 30 Minutes | Ivory White                 |
| 971601<br>97160W                                   | Timeout, With Hold | 60 Minutes | Ivory White                 |

| Catalog Number                           | Color        |
|------------------------------------------|--------------|
| <b>Replacement Knobs (without plate)</b> |              |
| PS55A1                                   | White        |
| PS55B1                                   | Ivory        |
| PS55G1                                   | Light Almond |

| VAC            | Hz | Amp | HP |
|----------------|----|-----|----|
| <b>Ratings</b> |    |     |    |
| 125            | 60 | 20  | 1  |
| 125T           | 60 |     | 7  |
| 250            | 60 | 10  | 1  |
| 277            | 60 | 10  |    |

## Features



- Eliminates the need for two switches.
- Fits standard toggle opening for easy ganging.
- Time range adjustable from 1-60 minutes.
- Easily installed.
- May control one or two loads simultaneously.
- Motor rated.
- Silent operation.
- Reliable solid-state construction.
- Energy saving.

| Catalog Number                                                   | Description               | Time Range               | Rating                      | Color       |
|------------------------------------------------------------------|---------------------------|--------------------------|-----------------------------|-------------|
| <b>Specification Grade Toggle Time Delay Switches Center Off</b> |                           |                          |                             |             |
| 973521<br>97352W                                                 | Double Pole, Double Throw | 1-60 Minutes, Adjustable | 500W, 1/3 HP, 120VAC, 60 Hz | Ivory White |

## Operation: Catalog Number 97352

- When toggle is up, one or two loads remain on.
- When toggle is down, load "A" is off, load "B" times-off at preset time. In the center position, both loads are off.

## Wiring Diagram: Single Timed Load Application



973521

All devices listed on this page conform to NEMA WD-1 and WD-6.