


1.0mmストロークバーチカルタイププッシュスイッチ

1.0mm-travel Compact-sized Vertical Type Push Switches

SPPH2 Series

ショートストローク 1mm、小形を誇るバーチカルタイプ。
Short-travel (1mm) small vertical type.



■ 特長

- ストロークは1 mm、ショートストローク。

■ Features

- Short travel-only 1 mm.

■ 用途

- 音響機器全般

■ Applications

- Audio equipment in general.

■ 主な仕様 Typical Specifications

項目 Item		仕様 Specification
最大定格 (抵抗負荷) Ratings (max.) (Resistive load)		0.1A 12V DC
接触抵抗 (初期/寿命後) Contact resistance (Initial performance / After lifetime)		30mΩ max./50mΩ max.
作動力 Operating force		2±1N
動作寿命 Operating life	無負荷 Without load	10,000 cycles
	負荷 With load	10,000 cycles (0.1A 12V DC)

■ 製品一覧 Products Line

枠 Frame	回路数 Poles	定格 Ratings	切換タイミング Changeover timing	端子 Terminal	取付方法 Mounting method	動作 Operating	移動量 Travel (mm)	全移動量 Total travel (mm)	電研納対応製品 Products for Densokunou	製品番号 Products No.
—	2	—	Non shorting	Straight	P.C.Board	Latching	1	1.5	—	SPPH210100
						Momentary				SPPH210500
				Snap-in		Latching			●	SPPH230100
						Momentary				SPPH230500

■ 注記
Notes

1. その他、詳細仕様についてはP.99をご参照ください。
2. 上記製品一覧以外にも保有している製品がございますので、ご希望の際はお問い合わせ願います。
1. For other detailed specifications, please see P.99.
2. Other switches than those included in the above list are also available, please inquire us for them if you are interested in them.

Unit : mm

■ 回路図 (A 方向より見る) **Circuit Diagram (Viewed from the Direction A)**

