


Cable Lug 32/35 mm DIN-Rail Terminals

Feed Through


SS 6




SS 8



SS 10



SS 12



Available Options	Version	SS 6	SS 8	SS 10	SS 12
	KrG	0498220000 0649820000	0498100000 1331900000	0484900000 1332000000	0498300000 1332100000
For TS 35 x 7	PA				
For TS 35 x 15/2-3	PA				
Dimensions					
Width / Length / Height mm (in.) with TS 35 x 7.5	↖	18/49.5/54.5 (.71/1.95/2.15)	36.5/60/68 (1.44/2.36/2.68)	36.5/60/68 (1.44/2.36/2.68)	36.5/60/72 (1.44/2.36/2.84)
	↗	18/40/62 (.71/1.58/2.44)	36.5/60/68 (1.44/2.36/2.68)	36.5/60/68 (1.44/2.36/2.68)	36.5/60/72 (1.44/2.36/2.84)
Technical Data					
Rated voltage / rated current / conductor size	UL				
	CSA				
	VDE	400 V* / 76 A / 16 mm²	1500 V* / 125 A / 35 mm²	1000 V* / 192 A / 76 mm²	1000 V* / 232 A / 95 mm²
Rated voltage / rated current / cross-section					
Continuous Currents					
of the terminals at max. conductor cross-section	A				
with cross-connection QL/Q 2 - 5 poles	A				
with cross-connection QL/Q 6 - 10 poles	A				
with VL 2	A				
Test voltage	k VAC				
Torque	Nm (lb. in.)				
Clamping screw	M				
End Plate (thickness mm)		Type	Part No.	Type	Part No.
		AP/TW(2)	1333200000	AP/TW(2)	1333200000
Partition (thickness mm)		Type	Part No.	Type	Part No.
	KrG	TW/HGW (2)	0607100000	0455860000	0455860000
	PA		0133200000	0133200000	0133200000
Jumpers		Type	Part No.	Type	Part No.
		QL 2	0284300000		
		QL 3	0273000000	QL 3	1578850000
		QL 4	2159500000	QL 3	1578850000
Marking Tags		Print			
Note: Part numbers shown are for a single card of pre-printed tags numbered 1-50. For additional information, see Accessories section.	Consecutive horizontal	DEK 5/5	0473460001	DEK 5/5	0473460001
	Consecutive vertical	DEK 5/5	0473560001	DEK 5/5	0473560001

See Accessories section for mounting rails, end brackets, test taps, additional marking material and accessories.