



General ordering data

Order No.	1272420000
Part designation	SAKT 4/35/LT O.STB
Version	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 35
EAN	4008190168483
Qty.	50 pc(s).

Product notes

Note, technical data	Two conductors with the same cross-section can be accommodated. 1.5 mm ² solid and 0.5...1.5 mm ² flexible
Function	Without StB
Note, accessories	To safe the test sockets use the SD-blade or bits with pilots!

Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1
No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 50 °C, + 130 °C
Product family	SAK Series
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Test-disconnect terminals

CSA rating data

Voltage (CSA)	300 V
CSA current	20 A
Min. cross-section (CSA)	AWG 26
Max. cross-section (CSA)	AWG 10

CSA rating data

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	4 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	0.13 mm ²
Clamping range, max.	6 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	10 mm
Clamping screw	M 2.5
Blade size	0.6 x 3.5 mm
Tightening torque range	0.4...0.7 Nm
Torque level with DMS electric screwdriver	1
Gauge to IEC 60947-1	A3
Solid, min.	0.5 mm ²
Solid, max.	6 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	4 mm ²
Flexible, min.	0.5 mm ²
Flexible, max.	4 mm ²
Flexible with ferrule, min. (DIN 46228/1)	0.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	4 mm ²
AWG conductor size, min.	AWG 26
AWG conductor size, max.	AWG 10
AWG conductor size, min.	0.13 mm ²
AWG conductor size, max.	5.26 mm ²

Dimensions

Width	6 mm
Height of lowest version	40 mm
Length	57.2 mm
TS 35 offset	28.5 mm

Disconnect terminals

Cross-disconnect	without
Integral test socket	No
Slitting	sliding
Tightening torque range	0.4...0.7 Nm
Torque level with DMS electric screwdriver	1

Rating data

Rated cross-section	4 mm ²
Rated voltage	400 V
Rated impulse voltage	6 kV
Rated current	32 A
Standards	IEC 60947-7-1

Rating data

Current with max. conductor	41 A
Pollution severity	3

UL rating data

Voltage (UL)	300 V
Current (UL)	20 A
Min. cross-section (UL)	AWG 22
Max. cross-section (UL)	AWG 12

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000902
ETIM 3.0	EC000902
eClass 4.1	27-14-11-26
eClass 5.0	27-14-11-26
eClass 5.1	27-14-11-26

Similar products

Order No.	Part designation	Version
0105820000	SAKT 1/35/DU1	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105420000	SAKT 1/35/LT	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105620000	SAKT 1/35/LT STB	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105720000	SAKT 1/35/QT1	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0124620000	SAKT 1/35/QT2	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0106020000	SAKT 2/35/LT 4STB	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
0105920000	SAKT 2/35/LT/STB	Disconnect and modular disconnect terminal, 6 mm ² , Screw connection, KrG, Medium yellow, TS 35
1272520000	SAKT 4/35/LT STB2.0	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 35
1289920000	SAKT 4/35/LT STB2.3	Disconnect and modular disconnect terminal, 4 mm ² , Screw connection, KrG, Medium yellow, TS 35