







SEE NOTE
2



NOTES:

1. [] DENOTE MILLIMETERS
2. SET SCREW IS 18-8 STAINLESS STEEL
3. OPERATING TEMPERATURE -40°F (-40°C) TO 250°F (121°C)
4. EXCELLENT CHEMICAL RESISTANCE TO THE FOLLOWING:
SULFURIC ACID, HYDROCHLORIC ACID, SODIUM HYDROXIDE, METHYL ETHYL KETON, ACETONE, 1,1,1 TRICHLOROETHANE, METHANOL, IPA, ASTM #3 OIL, SAE 20 OIL, ALCONOX, TOLUENE, MINERAL SPIRITS, GLACIAL ACETIC ACID, DIESEL FULE, HEPTANE, CELLOSOLVE ACETATE, AMMONIA, TURPENTINE, KEROSENE, WATER, AND GASOLINE
5. FOR USE INDOOR AND OUTDOOR
6. MAX SWITCH HANDLE WIDTH: .295 [7.5]

CAD FILENAME/LAYERS

100919AM_DC_C10905/01A

PANDUIT CORP. TINLEY PARK, ILLINOIS

MINIATURE CIRCUIT BREAKER LOCKOUT
PSL-MCB CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ± .1 (.XXX) ± .015
(.XX) ± .03 ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,

ALL DIMENSIONS ARE GIVEN

IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JHAC

MAT'L:

RED
33% GLASS-FILLED
NYLON

SCALE

1 : 1

DRAWING NO.

C10905

DWG
A
SIZE

0

4/28/11

JHAC

DRAWING RELEASE

6374

DATE
04/28/11

CHK'D

REV

DATE

BY

CHK

DESCRIPTION

ECN - R

CUST

SUP