






Materials:

- Insulator: Polyester, UL 94V-0, Standard
- Duplex Plating: Gold Plated on contact area, tin on solder area
- Contact: Phosphor Bronze
- Finish: Tin, Gold Plated

Electrical:

- Current Rating: 3 Amp
- Contact Resistance: $20\text{M}\Omega$ Max.
- Insulation Resistance: $1,000\text{M}\Omega$ Min
- Dielectric Withstanding Voltage: 500V
- Temperature Range: $-40^\circ\text{C} \sim +85^\circ\text{C}$
- Max Processing Temp: 230°C for 60 seconds
- Max Processing Temp: 260°C for 10 seconds



⊗ = Assmann Logo

RoHS
Compliant

ITEM NO

A-BL254D-A-Z-26-D

TITLE

Female Header - 26 pin, 2.54MM Pitch

Unit: $\text{MM} \pm 0.2\text{MM}$

ASSMANN
Electronics, Inc.

1840 W. Drake Drive, Suite 101 - Tempe, AZ 85283

Toll Free: 1-877-277-6266 Email: info@usa-assmann.com

THIS DRAWING IS UNPUBLISHED

© Copyright 2010 by Assmann Electronic Components
All International Rights Reserved