


Model 5343 Retractable Sheath Banana To BNC Male



FEATURES:

- Retractable Sheath Banana Plug provided for use with older test equipment.

MATERIALS:

Conn: 1st End-Retractable sheath banana plug:
Spring: Beryllium Copper per QQ-C-533,
Cond. H.T.Nickel plated per QQ-N-290, Class 2,
200/300 microinches.

Plug Body: Brass Rod, per ASTM B16-85,
Temper HO2. Nickel plated per QQ-N-290,
Class 2, 200/300 microinches.

Tip: Polypropylene. Color matches color of wire.
Compression Spring: Stainless Steel 302.

Insulation: Polypropylene molded to plug body
and wire. Color matches color of wire.

Wire: 20 AWG stranding 41 x 36 T.C., PVC insulated,
2.21 (.087) O.D. Color: One Black and one Red.

Molded Breakout: PVC molded to breakout leads
and cable. Color: Black

Cable: Shielded coaxial RG58C/U, 4.95 (.195) O.D.
Color: Black. Marking: "POMONA 5343-C-

XX". Conn: 2nd End-BNC Male Connector Body and
fittings: Tarnish resistant. Center Contact: Gold plated
per requirements of MIL-C-39012.

Strain Relief Boot: PVC molded to BNC plug and
cable. Color: Black

RATINGS:

Environmental: Operating Temperature: +50°C.
(+122°F.) Max.

Operating Voltage: Shield-Earth: 30VAC/60VDC,
Inner Conductor-Shield: 500 VRMS Max.

Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 5343-C-XX

XX=cable length, standard length: 36" (914) &
60" (1524)

Ordering Example: 5343-C-60 (1524)

Upon request other lengths may be quoted