

YAEV25-L4


BURNDY® PRODUCTS

YAEV25-L4

YAEV25-L4 : 1/0 NYLON HVY DTY RING 5



ACTIVE

[Assistant](#)[Add to Favorites](#)[Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Price request](#)

Specifications

[Download document](#)

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Strip length (Wire)	11/16 in.		
Stud Hole (Size)	5/8 in.		
Tongue Angle	Straight		
Tongue Width (in)	0.88 in.		
Wire Shroud	No		
Insulation Diameter (Max)	0.564 in.		
Physical			
Conductor Size	1/0 AWG		
Conductor Type	Commercial/Military Stranded Copper		
Insulation Type	Nylon		
Color Code	Blue		
Conductor Size (Range)	1/0 AWG		
Approvals / Certifications			
Military Listed	MIL-T-7928		
UL Listed	No		
CSA Certified	No		
Other Features			
Tongue Type	Ring		
Bulk Catalog Number	Same		
UPC	78181002758		
Keyword	smtermHD		