

## Heyco® Snub Bushings



Multiple Locking Steps for Panel Thickness up to .125" (3,2 mm)

Mounting Hole Diameter Range: .375" (9,5 mm) to .875" (22,2 mm)

| MOUNTING HOLE DIAMETER |      | APPROXIMATE CABLE DIAMETER* ACCOMMODATED |      | PART NO.<br>Black | DESCRIPTION | PART DIMENSIONS    |      |                     |      |
|------------------------|------|------------------------------------------|------|-------------------|-------------|--------------------|------|---------------------|------|
| in.                    | mm.  | in.                                      | mm.  |                   |             | A<br>Head Diameter |      | B<br>Overall Height |      |
| .375                   | 9,5  | 1/8                                      | 3,2  | <b>2034</b>       | K 375-125   | .46                | 11,7 | .42                 | 10,7 |
| .437                   | 11,1 | 3/16                                     | 4,8  | <b>2047</b>       | K 437-187   | .47                | 11,9 |                     |      |
| .500                   | 12,7 | 1/4                                      | 6,4  | <b>2057</b>       | K 500-250   | .56                | 14,2 |                     |      |
| .625                   | 15,9 | 3/8                                      | 9,5  | <b>2068</b>       | K 625-375   | .73                | 18,5 | .44                 | 11,2 |
| .750                   | 19,1 | 1/2                                      | 12,7 | <b>2088</b>       | K 750-500   | .91                | 23,0 |                     |      |
| .875                   | 22,2 | 5/8                                      | 15,9 | <b>2109</b>       | K 875-625   | 1.02               | 25,8 | .48                 | 12,3 |


Standard color black. Consult Heyco for white and other colors.

\*Consult Heyco for other Mounting Hole and Inside Diameter configurations. Our Axcell Rapid Response Team is ready to meet your requirements.



## Heyco® Sealing Washers

| WILL FIT THESE ELECTRICAL FITTING NPT TRADE SIZES | PART NO.<br>Black | DESCRIPTION | PART DIMENSIONS      |      |                       |      |                |     |
|---------------------------------------------------|-------------------|-------------|----------------------|------|-----------------------|------|----------------|-----|
|                                                   |                   |             | A<br>Inside Diameter |      | B<br>Outside Diameter |      | C<br>Thickness |     |
| 1/4                                               | <b>3258</b>       | SW 1/4      | .54                  | 13,7 | .80                   | 20,2 |                |     |
| 3/8                                               | <b>3259</b>       | SW 3/8      | .67                  | 17,0 | 1.01                  | 25,5 | .13            | 3,2 |
| 1/2                                               | <b>3260</b>       | SW 1/2      | .85                  | 21,6 | 1.24                  | 31,5 |                |     |
| 3/4                                               | <b>3261</b>       | SW 3/4      | 1.03                 | 26,2 | 1.50                  | 38,1 | .14            | 3,4 |
| 1                                                 | <b>3262</b>       | SW 1        | 1.28                 | 32,5 | 1.77                  | 45,0 | .18            | 4,4 |
| 1-1/4                                             | <b>3264</b>       | SW 1-1/4    | 1.66                 | 42,2 | 2.16                  | 54,8 |                |     |
| 1-1/2                                             | <b>3265</b>       | SW 1-1/2    | 1.86                 | 47,2 | 2.44                  | 62,0 | .16            | 4,1 |
| 2                                                 | <b>3257</b>       | SW 2        | 2.32                 | 58,9 | 2.93                  | 74,4 | .18            | 4,6 |



| Snub Bushing        |                                                                                                                                                                                       | Sealing Washers         |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| Material            | Nylon 6/6                                                                                                                                                                             | Thermoplastic Elastomer |
| Certifications      | Recognized under the Component Program of Underwriters' Laboratories, File E15331 (Snub Bushings only)<br>Certified by Canadian Standards Association, File 8919 (Snub Bushings only) |                         |
| Flammability Rating | 94V-2                                                                                                                                                                                 | 94-V0                   |
| Temperature Range   | -4°F (-18°C) to 221°F (105°C)                                                                                                                                                         |                         |



- The ID opens to accept the cable then closes firmly when installed into the mounting hole.
- Provide insulation plus light strain relief.
- Suitable for 1/8" (3,2 mm) to 5/8" (15,9 mm) diameter cable, tubing or hose.



- Make fittings and connectors liquid tight, dust tight, and oil tight at enclosure.
- Suitable for wet locations requiring a separate gasket between the box and fitting.
- Also suitable for other panel sealing applications.
- Easy to install since washers seal off on the perimeter, not on the connector threads.
- Special double sealing ridges compensate for minor unevenness at enclosure.

*Quick Specs*