

- Evaluate
 - FAQ's
- Design a Solution
 - Part Drawings
 - PDFDOMETOP Bar..
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Current refinements (click to remove) Search Tips

Text Search: 'BT6LH-C300'

Your search criteria matched only one product, shown below



- Greater resistance to damage caused by ultraviolet light and for high temperature applications up to 212°F (100°C) – indoor or outdoor use
- Dome-top head features unique patented design with round, smooth edges
- Stainless steel locking barb provides consistent performance, reliability and infinite adjustability through entire bundle range
- High strength and low thread force
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation (Miniature to Standard cross section)

Part Number	BT6LHC300
RoHS Compliancy Status	Compliant
Part Description	Cable Tie, Metal Barb, 21.2"L (538mm), Light Heavy, Heat Stabilized Weather Resistant, Black
Product Type	Cable Ties
Material	Heat Stabilized Weather Resistant Nylon 6.6
Color	Black
CSA Certified	Yes
UL Listed (File #E56854)	No
UL Recognized (File #E56854)	Yes
Length (In.)	21.2
Length (mm)	538
Width (In.)	0.275
Width (mm)	7.0
CE Compliant	Yes
Cross Section	Light-Heavy
Head Height (In.)	0.320
Head Height (mm)	8.1
Head Width (In.)	0.520
Head Width (mm)	13.2
Locking Style	Locking
Material Flammability Rating	V-2
Max. Bundle Diameter (In.)	6.00
Max. Bundle Diameter (mm)	152
Max. Continuous Use Temperature	212°F (100°C)
Min. Bundle Diameter (In.)	0.19
Min. Bundle Diameter (mm)	4.8
Min. Loop Tensile Strength (Lbs.)	120
Min. Loop Tensile Strength (N)	534
Plenum Rated	No
Pricing Description	Cable Tie, Metal Barb, 21.2" (538mm), Light Heavy, Heat Stabilized Weather Resistant, Black
Thickness (In.)	0.065
Thickness (mm)	1.7
Tool	GTH, GS4H, GS4EH, PTH, STH2, ST3EH
Min. Order UOM	PC
Min. Order Qty.	100
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.