

Switchcraft®

[Previous Page](#) | [Return to Index](#) | [Next Page](#)



MOLDED CABLE ASSEMBLIES 3.5 mm with Plugs

1. 35HRXXX35
2. 36HRXXX36
3. 35HRXXX84

[click here to download a schematic drawing](#)

(you will need to have Adobe Acrobat installed on your system to do this)



FEATURES AND BENEFITS

- Choose plug-to-plug or plug-to-stripped and tinned leads
- 3.5 mm plugs available as straight or right-angle

- Available in mono and stereo
- NOM.29 GA jacketed conductors (red and white) with copper spiral shield
- Cable O.D. 3.0 mm nom./.118" nom.
- Black cable

ORDERING

1. Order by part number ("XXX" is length in inches).
2. Contact Switchcraft for custom requirements.

PART NUMBERING SYSTEM

					
32 - Mono	H - Black	R - 3.0 mm nom. 2-conductor wire with spiral copper shield	Length (feet)		32 - Mono
33 - RA Mono			036 (3)		33 - RA Mono
35 - Stereo			072 (6)		35 - Stereo
36 - RA Stereo			144 (12)		36 - RA Stereo
					84 - Stripped and tinned
					90 - Straight Cut Off

SPECIFICATIONS

PLUG

Tip, Ring and Sleeve: Brass with nickel-plate

Flex Life: 5000 cycles minimum

Plug Insulator: ACETAL

[Previous Page](#) | [Return to Index](#) | [Next Page](#)

To search a category please click on the corresponding icon:



| [Connectors](#) | [Jacks and Plugs](#) |

| [Patch Panels, Patch Kits & Jackfields](#) | [Cable Assemblies and Patch Cords](#) | [Switches](#) |

All products shown are covered by Switchcraft's limited lifetime warranty.

| [Switchcraft home](#) |
[About Us](#) | [Products](#) | [What's New](#) | [Search](#) | [Contact Us](#)