





1 STAMP AMP 4W* 40-50 APPROX AS SHOWN

AMP WIRE RANGE	UL E13288 Listed
4 AWG SOLID OR STRANDED	4 AWG STRANDED
SP LR7189 Certified	MILITARY P/N AND CLASS
4 AWG SOLID OR STRANDED	NOT APPLICABLE

321060
AMP
PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS				THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN DK SCHRUM 150CT97		AMP Incorporated Harrisburg, PA 17105-3608		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	RECOMMENDED OPERATING TEMPERATURE: 170°C MAX		DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 [.008] 3 PLC ±- 4 PLC ±- ANGLES ±-	CHK MJ SPICER 150CT97	NAME TERMINAL, RING TONGUE, FLAG, SOLISTRAND™			
		VOLTAGE RATING: NOT APPLICABLE						APVD JL MECKLEY 150CT97		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 16.8-26.7mm² [33,100-52,600] CIR MILS SOLID OR STRANDED		MATERIAL COPPER PER ASTM B-152 ANNEALED	FINISH TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545	PRODUCT SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-321060	
FOR ORDER ENTRY	1-800-526-5142	CUSTOMER DRAWING				APPLICATION SPEC -	SCALE 2:1		SHEET 1 OF 1	REV C