










FCI AUTOMOTIVE
MAY 26 2004
DIVISION

UNCONTROLLED

FCI
MASTER COPY
WHEN IN RED

PART NO.	GRIP SIZE	GRIP TYPE	B	C	"D" DIA	"E" DIA	H	J	K	M	N		
SA-1015-12	10	1	5.08	6.86	2.54	4.32	11.68	15.24	5.08	3.96	15"		
SA-1115-12	11	2	5.08	7.62	1.52	3.05	11.68	15.24	5.08	4.26	15"30"		
SA-1315-12	13	2	4.57	6.60	1.02	2.54	9.40	12.19	4.57	4.01	20"30"		
SA-1415-12	14	1	3.56	5.08	1.52	2.03	9.40	12.19	3.56	3.56	25"		
SA-1815-12	18	1	2.79	4.32	1.02	2.03	6.60	8.64	3.18	3.25	32"		

6673	5/19/04	B-1	-	REDRAWN IN PRO-E HAD DIMENTIONED IN METRIC ONLY 0.33/0.20 WAS 0.33		T. LANGER	S. SIAM	S. SIAM
ECN NUMBER	DATE	W-D-Y	REVISION	ZONE	CHANGE DESCRIPTION	DRAWN BY	CHK. BY	APPR. BY
PRODUCT SPEC.	PACKAGING SPEC.		APPLICATION SPEC.		THIS DRAWING AND ALL OTHER INFORMATION CONTAINED HEREIN IS PROPRIETARY AND THE PROPERTY OF FCI. THIS DRAWING MAY NOT BE REPRODUCED, REPRODUCED OR DISCLOSED TO ANY THIRD PARTY WITHOUT THE EXPRESSED WRITTEN PERMISSION OF FCI.			
8-BULLET RECEPTACLE					MATERIAL: C422 FULL HARD 0.404 ± 0.015 THICK SURFACE FINISH: 2 MILS MAX			
TOLERANCES: ± 0.25 ANGLES ± 1		COLOR:		3RD ANGLE pro / eng. DIMENSION IN MILLIMETERS				
CONTRACT NO. N/A		DO NOT SCALE DRAWING		TOOL NO. D088	ECO Ltr. Code	N/A		
DRAWN BY 1-24-77 G EISENMANN					# 8 PIN RECEPTACLE (CONNECTOR TERMINAL)			
CHECKED BY - -					SA-1815-12			
APPROVED BY - -					CONNECTOR TERMINAL SCALE: 4:1			

FA02