






- | | |
|---|--|
| 1 | MATERIALS:
HOUSING: UL 94V-0, BLACK
CONTACT SPRING: STAINLESS STEEL
CONTACT BODY AND POST: BRASS
4-40 THREADED INSERT: BRASS |
| 2 | CONTACT BODY: .000030 MIN GOLD FOR A LENGTH OF
.200 MIN FROM MATING END. GOLD FLASH ON CONTACT |
| 3 | CONTACT POST: .000100 MIN TIN-LEAD OVER .000050 MIN NICKEL. |
| 4 | CONTACT POST: .000100 MIN TIN OVER .000050 MIN NICKEL. |
| 5 | RECOMMENDED PC BOARD HOLE SIZE FOR CONTACT
POST = .050±.003 DIA. |

OBSOLETE	.267	YES		213780-5
	.130	YES		213780-4
	.220	YES		213780-3
	.220	NO		213780-2
	.220	NO		213780-1
	DIM A	THREADED INSERTS	POST FINISH	PART NUMBER


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.LENKER		08/20/93		 TE Connectivity	
		CHK R.STONE		08/24/93			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —		NAME RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 23-24, CPC	
		0 PLC ± — 1 PLC ± — 2 PLC ± .005 3 PLC ± — 4 PLC ± — ANGLES ± ± —		PRODUCT SPEC 108-10024			
MATERIAL		FINISH		APPLICATION SPEC 114-10038			
		—		WEIGHT —			
		CUSTOMER DRAWING		SIZE A2		CAGE CODE 00779	
				DRAWING NO C-213780		RESTRICTED TO —	
				SCALE 2:1		SHEET 1 of 2	
						REV G	

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED P.C. BOARD LAYOUT
BOTTOM SIDE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.LENKER 08/20/93	 TE Connectivity			
DIMENSIONS: INCHES		CHK R.STONE 08/24/93				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME		
	0 PLC ± -		PRODUCT SPEC	RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 23-24, CPC		
	1 PLC ± -		108-10024			
	2 PLC ± .005		APPLICATION SPEC			
	3 PLC ± -		114-10038	SIZE A2	CAGE CODE 00779	DRAWING NO C-213780
	4 PLC ± -		WEIGHT -	RESTRICTED TO -		
	ANGLES ± -		CUSTOMER DRAWING	SCALE 2:1	SHEET 2 of 2	REV G
MATERIAL 		FINISH -				