



Quartz Crystal


MHz range

SMD-version


model	KX – 7
frequency	54,0 MHz
mode	fundamental
operating temperature	-20° ~ + 70°C
frequency tolerance at +25°C	± 15 ppm
temperature tolerance -20° ~ + 70°C	± 15 ppm
load capacitance C_L	19 pF
series resonance R_1 max.	15 Ohm
aging (first year)	± 2 ppm
shunt capacitance C_0 max.	3,0 pF
Pulling sensitivity	7ppm / pF typ.
drive level in μ W max.	350
RoHS	since production start
contents of reel	1000 pcs.
part no.	12.88788



soldering condition



suggested soldering pad



(mm) reel diameter 178 mm