



PART NAME	NBF SERIES PLASTIC NEMA BOX			PART No.	NBF-32026 & NBF-32126 & NBF-32226 & NBF-32326 & NBF-32426			REVISION DATE	6/28/2010
MATERIAL	FLAMMABILITY RATING	CONTINUOUS OPERATING TEMP.			FINISH: _____				
ABS	UL94-HB	-40°C ~ +60°C / -40°F ~ 140°F			BODY _____ LIGHT GRAY				
CLEAR PC	UL94-V0 UV STABILIZED	-40°C ~ +130°C / -40°F ~ 266°F			COVER _____ LIGHT GRAY OR CLEAR				
ABS / PC BLEND	UL94-5VA	-40°C ~ +85°C / -40°F ~ 185°F			LATCHES & HINGES _____ PLASTIC				
PBT / PC BLEND	UL94-5VA + UV (f1)	-40°C ~ +75°C / -40°F ~ 167°F			WALL MOUNTING BRACKETS__ STAINLESS STEEL & HARDWARE				



COVER

Top View Dimensions:
Overall Width: 15.748in [400.00mm]
Overall Height: 11.811in [300.00mm]
Internal Width: 12.805in [325.25mm]
Internal Height: 9.045in [229.75mm]

Side View Dimensions:
Overall Depth: 5.118in [130.00mm]
Internal Depth: 10.965in [278.50mm] INSIDE WIDTH MAX.
Internal Depth: 10.791in [274.08mm] INSIDE WIDTH MIN.

Section A-A Dimensions:
Overall Length: 14.728in [374.08mm]
Internal Length: 14.728in [374.08mm]

Section B-B Dimensions:
Overall Depth: 5.118in [130.00mm]
Internal Depth: 10.965in [278.50mm] INSIDE WIDTH MAX.
Internal Depth: 10.791in [274.08mm] INSIDE WIDTH MIN.

Section C-C Dimensions:
Overall Width: 15.748in [400.00mm]
Overall Height: 11.811in [300.00mm]
Internal Width: 12.805in [325.25mm]
Internal Height: 9.045in [229.75mm]

NOTES:

- 1) UNIT COMES COMPLETE WITH (4) WALL MOUNTING BRACKETS & (4) M5 x 10mm LG. SELF-TAPPING SCREWS. (NOT SHOWN)
- 2) BOXES DESIGNED TO MEET FOLLOWING STANDARDS: NEMA 1,2,4,4X, AND IEC529-IP65 REQUIREMENTS.

TOLERANCE:

ALL DIMENSIONS HAVE ± 0.039 in [± 1 mm]
TOLERANCE UNLESS OTHERWISE SPECIFIED.

PART NO.	MATERIAL		USE
	BODY	COVER	
NBF-32026	ABS	ABS	INDOOR
NBF-32126	ABS / PC	ABS / PC	INDOOR
NBF-32226	ABS / PC	CLEAR PC	INDOOR
NBF-32326	PBT / PC	PBT / PC	OUTDOOR
NBF-32426	PBT / PC	CLEAR PC	OUTDOOR