

Clifa® press-in nut/stud ...

Clifa®-press-in nuts and Clifa® studs are threaded inserts made of steel with a specially formed shank or head.

Clifa®-press-in nuts and Clifa® studs can also be supplied in rust-proof material, and the nuts additionally in light alloy.

Clifa®-threaded inserts are pressed into moulded components with prepunched receiving holes. During this process, the material flows out of the area of the hole wall into the gear ring / the annular grooves of the Clifa® threaded inserts. A permanent connection is formed.

Several Clifa® inserts can be installed in a single work process. The fastening screw is always screwed in from the opposite side.

Fields of application

Clifa® press-in elements serve as a screw point mainly on moulded parts of steel or light metal. They may also be used as spacers.

Product features

- Clifa® is torque-proof, capable of withstanding high loads.
- It has minimal outside dimensions for space and weight-saving
- The thread is wear-resistant, clean and true to gauge
- Mounting in drilled, punched or lasered receiving holes
- Do not countersink drill holes in the component
- Can be used in surface-treated, galvanized or unweldable materials
- Clifa® is not pressed out during the screwing process.
- The component material must be softer than the Clifa® element



Specifications

Works Standard sheets Clifa®
Pages 11 to 20

High-performance installation equipment for short cycle times in largescale production on request.



Clifa® installation ...

Installation


The receiving hole is punched, lasered or drilled **but not deburred or countersunk**.

With punched holes, Clifa® is pressed in from the punching burr side. The press-in process takes place on a plane parallel basis using a customary press with adjustable pressure level, until the surface of the shoulder in the Clifa® pressin nut comes to rest flat against the surface of the sheet metal.


In the case of the Clifa®-SP/SPD/SPS stud, the head must be fully pressed in and come to rest flush with the surface of the sheet metal.

Pressure which is too high or applied only on one side as well as inclined support surfaces must be avoided wherever possible.

Examples for mounting



Press-in nut Clifa®



Press-in stud Clifa®-SP

Fig. 8



Special request

short length
standoff bushings for metals
standoff bushings for plastics
threaded press-in stud
Flush surface on the press-in side of the nut element (/- thread closed on one side)
Grub screw for thin sheet thicknesses
Grub screw for high load values
threaded press-in stud for lower press-in force


We recommend

Clifa®-M	(Works Standard 500 0 to 503 0)
Clifa®-AM	(Works Standard 503 8 to 525 8)
Clifa®-AL	(Works Standard 503 6 to 525 6)
Clifa®-ABO/-ABG	(Works Standard 570 0 to 571 0)
Clifa®-SPD	(Works Standard 5.. 2)
Clifa®-SA	(Works Standard 515 4 to 534 4)
Clifa®-SAD	(Works Standard 515 9 to 534 9)

Application

Clifa®-SP press-in grub screws are processed flush with the surface – see diagram –, and are used to manufacture wear-resistant, highly resilient screw connections in thin-walled moulded parts made of:

- Steel
- Stainless steel
- Brass
- Copper
- Light metal, etc.



Dimensions in mm

Article number	Internal thread	Workpiece thickness	External diameter	Hole diameter	Minimum spacing	Tightening torque of the nut (guideline values for sheet metal) ≤ Nm
	A	≥ M	E	L +0,05	≥ W	
5.. 000 025 ...	M 2,5	1,0	4,0	2,5	3,5	0,7
5.. 000 030 ...	M 3	1,0	4,6	3,0	4,0	1,5
5.. 000 040 ...	M 4	1,0	5,9	4,0	5,0	2,9
5.. 000 050 ...	M 5	1,0	6,5	5,0	5,0	6,0
5.. 000 060 ...	M 6	1,5	8,5	6,0	5,0	10,0
5.. 000 080 ...	M 8	1,5	10,0	8,0	6,0	20,0

Article number first group of digits (selection series)	Length B*) ±0,2	Available					
		M 2,5	M 3	M 4	M 5	M 6	M 8
506 000	6,0	X	X	X	X		
508 000	8,0	X	X	X	X	X	
510 000	10,0	X	X	X	X	X	X
515 000	15,0	X	X	X	X	X	X
520 000	20,0	X	X	X	X	X	X
525 000	25,0	X	X	X	X	X	X
530 000	30,0			X	X	X	X
534 000	34,0			X	X	X	X

Example for finding the article number

Press-in stud Clifa®-SP, M3 tempered, zinc plated and blue passivated steel, 10 mm long, with serrations at the head for sheet metal thickness 1,2 mm: Clifa®-SP 510 000 030.110

Materials

Steel tempered, zinc plated, blue passivated **

Steel tempered, zinc-nickel plated, transparent passivated **

Stainless steel

Article no. (fourth group of digits) 110

Article no. (fourth group of digits) 143

Article no. (fourth group of digits) 500

Further dimensions on request.

Threaded ends

Press-in grub screws with differing threaded ends on request, see data sheet, page 25.

Tolerances

ISO 2768-m

Thread

Stud thread A: as per ISO 6g, imperial thread available in all customary sizes.

Press-in force

Guideline values for press-in force, see page 24

*) Length B

available up to 60 mm

**)


Press-in stud in tempered steel, available in customary strength classes.

Application

Clifa®-SPD press-in grub screws are processed flush with the surface – see diagram –, and are used to manufacture wear-resistant, highly resilient screw connections in thin-walled moulded parts made of:

- Steel
- Stainless steel
- Brass
- Copper
- Light metal, etc.

Due to the low height of the serrations, Clifa®-SPD is suitable for use in lower moulding strengths than necessary with Clifa®-SP.



Dimensions in mm

Article number	Internal thread	Workpiece thickness	External diameter	Hole diameter	Minimum spacing	Tightening torque of the nut (guideline values for sheet metal) ≤ Nm
	A	≥ M	E	L +0,05	≥ W	
5.. 200 025 ...	M 2,5	0,8	4,0	2,5	3,5	0,7
5.. 200 030 ...	M 3	0,8	4,6	3,0	4,0	1,5
5.. 200 040 ...	M 4	0,8	5,9	4,0	5,0	2,9
5.. 200 050 ...	M 5	0,8	6,5	5,0	5,0	6,0
5.. 200 060 ...	M 6	0,8	8,5	6,0	5,0	10,0
5.. 200 080 ...	M 8	0,8	10,0	8,0	6,0	20,0

Article number first group of digits (selection series)	Length B*) ±0,2	Available					
		M 2,5	M 3	M 4	M 5	M 6	M 8
506 200	6,0	X	X	X	X		
508 200	8,0	X	X	X	X	X	
510 200	10,0	X	X	X	X	X	X
515 200	15,0	X	X	X	X	X	X
520 200	20,0	X	X	X	X	X	X
525 200	25,0	X	X	X	X	X	X
530 200	30,0			X	X	X	X
534 200	34,0			X	X	X	X

Example for finding the article number

Press-in stud Clifa®-SPD, M3 tempered, zinc plated and blue passivated steel, 10 mm long, with serrations at the head for sheet metal thickness 0,8 mm: Clifa®-SPD 510 200 030.110

Materials

Steel tempered, zinc plated, blue passivated **

Steel tempered, zinc-nickel plated, transparent passivated **

Stainless steel

Article no. (fourth group of digits) 110

Article no. (fourth group of digits) 143

Article no. (fourth group of digits) 500

Further dimensions on request.

Threaded ends

Press-in grub screws with differing threaded ends on request, see data sheet, page 25.

Tolerances

ISO 2768-m

Thread

Stud thread A: as per ISO 6g, imperial thread available in all customary sizes.

Press-in force

Guideline values for press-in force, see page 24


*) Length B

available up to 60 mm

**)

Press-in stud in tempered steel, available in customary strength classes.


Dimensions in mm



Anvil for: Clifa®	Hole L1 +0,1	Countersink for serrations N +0,1	Press-in force kN
M 2,5	2,6	3,4	8,9 to 12
M 3	3,1	4,0	10,5 to 19
M 4	4,1	5,2	16 to 25
M 5	5,1	6,4	29 to 35
M 6	6,1	7,6	30 to 50
M 8	8,1	10,2	30 to 60

The press-in force F is dependent on the Clifa® dimension, the material and the thickness of the shaped component and also the type of serration at the head. The Clifa® head must be fully embedded and must come to rest flush with the surface of the sheet metal. Excessive force must be avoided. The hole diameter of the part to be screwed on $\approx A + 0,6$ mm.


Dimensions in mm



Anvil for: Clifa®	Hole L1 +0,1	Countersink for serrations N +0,1	Press-in force kN
Ø 5,0	5,1	6,4	29 to 35

The press-in force F is dependent on the Clifa® dimension, the material and the thickness of the shaped component and also the type of serration at the head. The Clifa® head must be fully embedded and must come to rest flush with the surface of the sheet metal. Excessive force must be avoided. The hole diameter of the part to be screwed on $\approx A + 0,6$ mm.

Dimensions in mm



Anvil for: Clifa®	Hole L1 +0,1	Countersink for serrations N +0,1	Press-in force kN
M 3	3,1	4,0	9,0 to 15,0
M 4	4,1	5,2	14,5 to 38
M 5	5,1	6,4	21 to 42
M 6	6,1	7,6	21 to 50
M 8	8,1	10,2	21 to 60
M 10	10,1	12,2	32 to 84


The press-in force F is dependent on the Clifa® dimension, the material and the thickness of the shaped component and also the type of serration at the head. Excessive force must be avoided. The hole diameter of the part to be screwed on $\approx A + 0,6$ mm.

Application


Depending on the demands placed on the Clifa® press-in grub screws, we offer a variety of threaded ends. Further threaded ends on request.

Sub-function	Type of threaded end			
	KKV	KK	PN	KK-MAG
Protection of start of thread	↘	↗	↗	↗
Larger displacement when fastening	↘	→	↗	↗
Prevention of tilting when fastening	↘	→	→	↗
Usable thread length (Version for components of the same length)	↗	→	→	↘

Type of threaded end: **KKV**
DIN EN ISO 4753 (RL)



Type of threaded end: **KK**



Type of threaded end: **PN**



Type of threaded end: **KK-MAG**



Fasteners for special applications ...

**Press-in stud
with special part-end**



**Rivet bushing with
Double riveting contour**



**Press-in nut with
Three cross-holes**



**Press-in stud
with segmented head**



**Rivet bushing with fine
thread on outer diameter**



**Rivet bushing with
special sealing contour**



**Bolt with t-groove for
fixing/locking of screw-in
elements**



**Press-in nut with
hexagonal head**



**Press-in nut with three
knurls on outer diameter**

