

Wiha 3/8" Socket Accessories



602 57 3/8" Universal Joint Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 57	1.97	50	.13



602 58 3/8" Swivel Handle Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 58	8.82	224	.47



602 59 3/8" Converter To 1/4" Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 59	.98	25	.07



602 60 3/8" Converter To 1/2" Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 60	1.38	35	.11



602 61 3/8" Square Coupler Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 61	.98	25	.03

Wiha 3/8" Spark Plug Sockets



602 62 Spark Plug Socket DIN 3124 / ISO 2725


Hard chrome finish, head polished extra deep. Ball retaining groove with rubber insert. 3/8" Drive. 12 point

Item					
No.	Inch	mm	mm	Inch	wt.
602 62	13/16"	20.6	65	2.6	.31

602 63 Spark Plug Socket DIN 3124 / ISO 2725

Hard chrome finish, head polished extra deep. Ball retaining groove with rubber insert. 3/8" Drive. 12 point

Item				
No.	mm	mm	Inch	wt.
602 63	18	65	2.6	.28



6 Point



602 64 Spark Plug Socket DIN 3124 / ISO 2725

Hard chrome finish, head polished extra deep. Ball retaining groove with rubber insert. 3/8" Drive. 6 point

Item					
No.	Inch	mm	mm	Inch	wt.
602 64	5/8"	16	65	2.6	.22