


LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	7000pF GMV
TEMP. RANGE	-55°C TO 125°C
CURRENT	5 AMP MAX.
WORKING VOLTAGE	85°C -- VDC MAX. 125°C 50 VDC MAX.
D.C. RESISTANCE	0.1ohms MAX.

MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
3	-
10	14
30	-
100	70
300	70
1 GHz	70



MARKING:

PART: API 312 (FAIRVIEW)
 API 312M (MEXICO)

BAG:
 51-729-312
 DATE CODE
 QTY./BAG (50 MAX.)

	32	31	30	29	28	REV. NID.	TOLERANCES UNLESS OTHERWISE SPECIFIED		FAIRVIEW PENNSYLVANIA
	CN #21355	CN 70197-ENG	CN 19756-CPD	CN 190752	CN. 184953 REDRAWN	CHANGE NOTICE	Fractions ± 1/64		
							Dec. .xx±	Date 8-11-16	RESIN SEAL FILTER
							Dec. .xxx± .005	Engr. B.DEVINE	51-729-312
							Angles ±0° 30'	Scale NONE	
							CODE IDENT. NO. OLSP2		