

Actual information about approvals can be found on
<http://www.schurter.com/approvals>



4752
Quadbloc

F

 70 °C



Description

- Panel mount:
Snap-in version from front side
- 2 Functions:
Module of 4 outlets, Pin temperature 70 °C, Protection class I
- Solder terminals or quick connect terminals

Characteristics

- Busbar is of single piece (no soldering)
- Insulation cover on the rear-side
- Qualified for use in equipment according IEC/EN 60950

Other versions on request:

- for protection class II


Technical data

Ratings IEC	10 A / 250 VAC; 50 Hz
Ratings UL/CSA	15 A / 250 VAC; 60 Hz
Dielectric strength	> 2 kVAC between L-N > 2 kVAC between L/N-PE (1 min/50 Hz)
Allowable operation temp.	-25 °C to 70 °C
Degree of protection	from front side IP30 acc. to IEC 60529
Protection class	Suitable for appliances with protection class I acc. to IEC 61140

Terminals	Solder terminals or quick connect terminals
Panel thickness s	Snap-in/1.2/1.5/2/2.5/3 mm tolerance +0.0/-0.1
Materials: Housing	Thermoplastic, black, UL 94V-0
Appliance-inlet /-outlet	F acc. to IEC/EN 60320-2-2, UL 498 CSA C22.2 no. 42 (for cold condition) pin-temperature 70 °C, 10 A, Protection class I

Dimensions

Quadbloc 4752



Panel cut-out 96,2 x 32,5 mm, corner radius max. 1 mm

Variants

Order Number	Panel thickness s [mm]	Terminals	Length [mm]	Length L2 [mm]
4752.3200	1	Quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.8200	1.2	Quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.4200	1.5	Quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.5200	2	Quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.6200	2.5	Quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.7200	3	Quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.3400	1	Solder terminals 4 x 0.8 mm	100	96.2
4752.8400	1.2	Solder terminals 4 x 0.8 mm	100	96.2
4752.4400	1.5	Solder terminals 4 x 0.8 mm	100	96.2
4752.5400	2	Solder terminals 4 x 0.8 mm	100	96.2
4752.6400	2.5	Solder terminals 4 x 0.8 mm	100	96.2
4752.7400	3	Solder terminals 4 x 0.8 mm	100	96.2
4752.3000	1	Solder terminals 4 x 0.8 mm and quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.8000	1.2	Solder terminals 4 x 0.8 mm and quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.4000	1.5	Solder terminals 4 x 0.8 mm and quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.5000	2	Solder terminals 4 x 0.8 mm and quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.6000	2.5	Solder terminals 4 x 0.8 mm and quick connect terminals 6.3 x 0.8 mm	100	96.2
4752.7000	3	Solder terminals 4 x 0.8 mm and quick connect terminals 6.3 x 0.8 mm	100	96.2

Please note, all quadblocs are available in protection-class II upon request.

Cord retaining clamp see accessories

Packaging unit

50 Pcs

Accessories

ACCESSORIES