





LOC AD	DIST 0	P	F	REVISIONS						
				ZONE	LTR	DESCRIPTION			DATE	APPD
					Y	REV PER 0G3C-0104-01			25SEP01	J0

1. RECEPTACLE ACCEPTS A .008-.014 THICK I.C. LEAD.
2. TUBE LOADED FOR AUTOMATIC INSERTION.
- 3


TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 4

TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN-LEAD (93/7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 5

SPECIAL PACKAGING.



SECTION A-A
SCALE 10:1



RECOMMENDED MOUNTING HOLE PATTERN
SCALE 4:1

SUPSD BY 390261-8	3	TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	5-641932-1
OBSOLETE		TINNED	PH05.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641932-5
	3		PH05.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641932-4
SUPSD BY 390261-8		TINNED	PH05.BRZ. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641932-3
	3		BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641932-2
SUPSD BY 390261-8		TINNED	BE.CU. .006 THK	GLASS-FILLED THERMOPLASTIC, 94V-0, BLACK	2-641932-1
CONTACT FINISH		CONTACT MAT'L		HOUSING MATERIAL	PART NO.

				PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON : 2 PL DEC ±- 3 PL DEC ±.005 ANGLES ±0°30'		DR 8-17-87 M.CYRUS		AMP AMP INCORPORATED Harrisburg, Pa. 17105	
		CHK 8-31-87 R.MILLER			
		APPD 9-4-87 J.LAMBERT			
MATERIAL SEE TABLE		APPD 9-4-87 J.GRAY		SOCKET ASSY, DIP, LADDER, 24 POS, DIPLOMATE DL	
		PRODUCT SPEC 108-1066			
FINISH SEE TABLE		APPLICATION SPEC 114-1049			
		WEIGHT -		D 00779 641932	
		SCALE 5:1		SHEET 1 OF 1	