

[Twisted Pair & Flat
Phone Cable](#)[Fiber Optic Cable](#)[Coaxial Cable](#)[Electrical and Industrial](#)[Bench/Other Hand Tools](#)[What's New](#)[Coaxial Cable > Crimpers > 1300 Series](#)[We also suggest](#)

RG8/11/213 1300 Series Crimper

Part number: 1365  Technical

Part numbers

Tool & Die: 1365

Die only: 2656

Description

Crimps N-type coaxial plugs.

Type

RG8, RG11, RG213

Crimp size

.429/.100/.080" HEX

Connector style

Kings, ADC, Amphenol, etc.



LAN
ProNavigator™
Tester



Datacomm &
Telecom
Scissors



LAN & A/V
Cable-Check™



Ultimate
Technician Tool
Kit



Combo
UTP/Coax
SureStrip®
Cutter/Stripper