

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210230629](#)
Status: **Active**
Overview: [mPm DIN Valve Connectors](#)
Description: mPm DIN Valve Connector, Form A-18mm, PG9 Internal Threads, 3 Pole Plus Ground, Black, Nitrile Gasket, Bulk Pack Mounted

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-121023-C81-001 \(PDF\)](#)


General
Product Family Field Attachable / Accessories
Series [121023](#)
Form A - 18mm
IP Rating IP65, IP67
Material - Contact Brass
Overview [mPm DIN Valve Connectors](#)
Product Name mPm
Type Field Attachable Connector
UPC 883906484439

Physical
Cable Diameter N/A
Coupling Type Internal Thread
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway None
Material - Connector Body Polypropylene
Material - Coupling Nut N/A
Material - Plating Mating Silver
Net Weight 29.592/g
Orientation 90° Angle
Pitch - Mating Interface 18.00mm
Poles 3
Temperature Range - Operating -40°C to +90°C
Wire Size AWG N/A

Electrical
Current - Maximum per Contact 16.0A
Voltage - Maximum 250V AC / 300V DC

Material Info
Engineering Number C81309N21

Reference - Drawing Numbers
[Packaging Specification](#) PK-121023-C81-001
[Sales Drawing](#) SD-121023-008



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2020)4578-DC (25 June 2020)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[121023](#) Series