



Sample photo

Order symbol: PCM 100/60 G
Product nbr: 6016301
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038005
El. number:
Finland: 3421631
Electric No. Denmark: 8212027006
Electric No. Italy: 7341010
Electric No. Sweden: 2535303

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
mm:	130	80	60	MIN 5	DIN-15 Mounting rail
inch:	5.1	3.1	2.4	MIN 10	DIN-15 Mounting rail
				MIV 5	DIN-35 Mounting rail
				MIV 10	DIN-35 Mounting rail
Materials:				FP A 100/130	Front plate (Aluminium)
Material:	Polycarbonate				
Base colour:	RAL 7035 -light grey				
Cover screws material:	Polyamide				
Cover colour:	RAL 7035 -light grey				
Cover screws colour:	Grey				
Gasket material:	TPE				
Temperatures:					
Temperature °C (short term):	-40 ... 120 °C				
Temperature °C (continuous):	-40 ... 80 °C				
Temperature °F (short term):	-40 ... 250 °F				
Temperature °F (continuous):	-40 ... 175 °F				
Accessories:					
MIV 100	Mounting plate (Galvanized steel)				

