


36 3642


RAST 5 connectors, pitch 5.0 mm



RAST 5 tab header, angular, with topside lock

Approvals:





Counterparts

|                             |                        |                        |
|-----------------------------|------------------------|------------------------|
| <a href="#">3611</a>        | <a href="#">3615</a>   | <a href="#">3615-1</a> |
| <a href="#">3615-2</a>      | <a href="#">3615-3</a> | <a href="#">3623</a>   |
| <a href="#">3623 01 V01</a> | <a href="#">3626</a>   |                        |

36 3642

| Designation | Pole Number | PU (Pieces) | MDQ (Pieces) | Dimensions |        |        |
|-------------|-------------|-------------|--------------|------------|--------|--------|
|             |             |             |              | A (mm)     | B (mm) | C (mm) |
| 3642 02     | 2           | 250         | 1000         | 5          | 10.2   | 12.3   |
| 3642 03     | 3           | 250         | 1000         | 10         | 15.2   | 17.3   |
| 3642 04     | 4           | 250         | 1000         | 15         | 20.2   | 22.3   |
| 3642 05     | 5           | 250         | 1000         | 20         | 25.2   | 27.3   |
| 3642 06     | 6           | 250         | 1000         | 25         | 30.2   | 32.3   |
| 3642 07     | 7           | 250         | 1000         | 30         | 35.2   | 37.3   |
| 3642 08     | 8           | 250         | 1000         | 35         | 40.2   | 42.3   |
| 3642 09     | 9           | 250         | 1000         | 40         | 45.2   | 47.3   |
| 3642 10     | 10          | 250         | 1000         | 45         | 50.2   | 52.3   |
| 3642 11     | 11          | 250         | 1000         | 50         | 55.2   | 57.3   |
| 3642 12     | 12          | 250         | 1000         | 55         | 60.2   | 62.3   |

Designation to be completed by further details (e.g. for keying, color or material options).

**Packaging:**

in bulk, in a cardboard box