

[Home](#) > [All AC Axial](#)

AC Axial Fans - 3115PS-12W-B20 Specifications

[Request Quote](#)[See Stores](#)

Part Specifications		
Product Type	AC Axial Fans	
Part Number	3115PS-12W-B20-A00	3115PS-12W-B20-A00
Rated Voltage	115 (V)	115 (V)
Frequency	60 (Hz)	50 (Hz)
Air Flow	24.0 (CFM)	21.0 (CFM)
Air Flow	0.68 (m³/min)	0.60 (m³/min)
Size [S]	80 (mm)	80 (mm)
Thickness [L]	38 (mm)	38 (mm)
Starting Voltage	75 (V)	75 (V)
Current	0.070 (A)*1	0.080 (A)*1
Input Power	4.50 (W)+10%/-2	5.00 (W)+10%/-2
Speed	2300 (min-1)*3	2100 (min-1)*3
Maximum Static Pressure	0.12 in H2O	0.10 in H2O
Maximum Static Pressure	29.4 (Pa)*3	24.5 (Pa)*3
Noise	32 (dB)*2	29 (dB)*2
Mass	270 (g)	270 (g)
IP Rated	No	--
PDF	 download PDF	 download PDF
Lead Wire Count	2	2
Termination	Lead	Lead
Bearing Type	Ball	Ball
Sensor	No	No
Mounting Type	Flange	Flange
Lead Wire Type	Standard	Standard

3115PS-12W-B20 AC Axial Fans can be an integral part of a cooling solution for your heat-generating applications. Review the part specifications provided to understand how 3115PS-12W-B20 can work with your system. Ready to purchase 3115PS-12W-B20? Explore the inventory currently available through our distributors below. You can also learn about similar AC Axial Fans parts in inventory by following the links provided. Let NMB Technologies Corporation help you find the cooling solutions you need.


PDFs

 [3115ps.pdf](#)


CAD

 [3115PS IGES CAD](#) [3115PS Pro-E CAD](#) [3115PS Solidworks](#)[CAD](#) [3115PS STEP CAD](#)

RoHS Certificates

[RoHS Cert. for](#)[3115PS-12W-B20-A00](#)

3115PS
PQ Curve



3115Ps Front
2D CAD Image



3115Ps Right
Side
2D CAD Image

Similar Parts Available

Part Number	
3115FS-12T-B00-A00	Part Details >
3115FS-12T-B10-A00	Part Details >
3115FS-12T-B20-A00	Part Details >
3115FS-12T-B30-A00	Part Details >
3115FS-12W-B10-A00	Part Details >
3115FS-12W-B20-A00	Part Details >
3115FS-12W-B30-A00	Part Details >
3115FS-23T-B10-A00	Part Details >
3115FS-23T-B20-A00	Part Details >
3115FS-23T-B30-A00	Part Details >
3115FS-23W-B10-A00	Part Details >
3115FS-23W-B20-A00	Part Details >
3115FS-23W-B30-A00	Part Details >

3115PS-12T-B30-A00	Part Details >
3115PS-12T-B30-A00	Part Details >
3115PS-12W-B30-A00	Part Details >
3115PS-12W-B30-A00	Part Details >
3115PS-23T-B20-A00	Part Details >
3115PS-23T-B30-A00	Part Details >
3115PS-23W-B20-A00	Part Details >
3115PS-23W-B30-A00	Part Details >

Your graphics card does not seem to support WebGL.
Find out how to get it here.