


Terminal Block Tri-Barrier

158-P02DT39B, 158-P03DT39B, 158-P04DT39B, 158-P05DT39B,
158-P06DT39B, 158-P07DT39B, 158-P08DT39B, 158-P09DT39B,
158-P10DT39B, 158-P11DT39B, 158-P12DT39B

KOBI **CONN**

Terminal Block Tri-Barrier



Dimensions: mm (In.)

P	02P	03P	04P	05P	06P	07P	08P	09P	10P	11P	12P
U mm	8.25	16.5	24.75	33.0	41.25	49.5	57.75	66.0	74.25	82.5	90.75
V mm	17.4	25.65	33.9	42.15	50.4	58.65	66.9	75.15	83.4	91.65	99.9

ELECTRICAL SPECIFICATIONS

Rating:	300V 20A
Pitch:	8.25 mm
Insulation withstands voltage:	AC 2000V/Min
Insulation resistance:	500MΩ or more at DC500V
Temperature range:	-40°C~ +105°C
Screw torque value:	10kg-cm
Electric wire:	22~12 AWG

MATERIAL SPECIFICATIONS

Screw:	steel, Ni plated 6 -32UNC
Solder pin:	brass, Tin plated, 0.8t
Housing:	PA66, black

Date Last Revised: 10-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300766

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[158-P08DT39B](#) [158-P06DT39B](#) [158-P11DT39B](#) [158-P03DT39B](#) [158-P12DT39B](#) [158-P02DT39B](#)