







- 1 RECEPTACLE ACCEPTS A .008—.014 THICK I.C. LEAD.
- 2 TUBE LOADED FOR AUTOMATIC INSERTION.
- 3 BECU CONTACT —PLATED WITH TWO .000030 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 4 PHOS. BRZ CONTACT — PLATED WITH TWO .000015 MIN THK. GOLD STRIPES IN CONTACT AREA WITH TIN ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.
- 5 GLASS FILLED THERMOPLASTIC, 94V—0, BLACK

(B)	OBSOLETE		1.100	11	1.195	24	1-1825094-7.
(B)	OBSOLETE		.900	9	.995	20	1-1825094-6.
			.800	8	.895	18	1-1825094-5.
(B)	OBSOLETE		.700	7	.795	16	1-1825094-4.
			.600	6	.695	14	1-1825094-3.
			.300	3	.395	8	1-1825094-2.
			.200	2	.295	6	1-1825094-1.
(B)	OBSOLETE		1.100	11	1.195	24	1825094-7.
(B)	OBSOLETE		.900	9	.995	20	1825094-6.
			.800	8	.895	18	1825094-5.
(B)	OBSOLETE		.700	7	.795	16	1825094-4.
			.600	6	.695	14	1825094-3.
			.300	3	.395	8	1825094-2.
			.200	2	.295	6	1825094-1.
		CONTACT & FINISH	DIM. C B	SPCS	DIM. A	POSITION	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.S.VISWESWARA		21APR05		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		DIP SOCKET ASSY, LADDER, DIPLOMATE, .300 CL, LEAD FREE	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± ± 0°30'		PRODUCT SPEC 108-1066		DIP SOCKET ASSY, LADDER, DIPLOMATE, .300 CL, LEAD FREE	
MATERIAL		FINISH		APPLICATION SPEC 114-1049		RESTRICTED TO	
SEE TABLE		SEE TABLE		WEIGHT —		SIZE A2	
				CAGE CODE 00779		DRAWING NO C-1825094	
				CUSTOMER DRAWING		SCALE 5:1 SHEET 1 of 1 REV B	