



4

3

2

1

UNIT:mm



Electrical test:

1. 100% short, open, miswire test



2. Conduct resistance: 5 Ohm(max)

3. Insulation resistance: 10Mohm(min)

4. dielectric test: DC 300V

NOTE:

1. 小PE袋/大PE袋对应料号,包袋数量及时间印刷样式:



⑪	扎带	2	黑色 L=80mm
⑩	大PE袋	1/10	透明PE袋大小尺寸: 280*330*0.05mm 印刷黑色"MADE IN CHINA"+*10PCS*及印生产周期,有透气孔.
⑨	小PE袋	1	透明PE袋: 130*230*0.05mm 印刷黑色"MADE IN CHINA"+*1PC*及印生产周期,有透气孔.
⑧	外模	15g	黑色 45P PVC (MOLD NO: CH003)
⑦	铁粉芯	2	铁粉芯 OD12.5,6*120
⑥	外模	5g	黑色 PVC-45P (MOULD NO: WM-40)
⑤	内模	0.35g	透明LD-PE (MOULD NO: NM-86)
④	外模	4.5g	黑色 PVC-45P (MOULD NO: WM-116)
③	线材	1	USB2.0 UL2725 (28AWG*1P+24AWG*2C) +AEB(48 ALMG) L=2000±10MM 外被: 黑色 OD:4.5mm
②	接头	1set	USB A公制破式一体式长铁壳镀镍 中接头,铁壳厚度0.3白胶芯白后盖,0.9*1.1端子青铜镀金
①	接头	1	MICRO USB 5P B公 PIN G/F 外壳镀镍 黑胶芯
NO.	NAME	QTY	SPECIFICATION

4

3

2

1

CnC Tech, LLC			
Industrial Cable and Connector Technology			
DRAWN BY	LYNDON	DRAWING NO	VC/LJQ-094-098-C
CHECKED BY		CUSTOMER	CNC
APPROVAL BY		ITEM NO.	102-1492-BL-F0200
DECIDED BY		DATE	2016-05-24
VERSIONS/EDITION	A/0	PROJECTION	