

[Home](#) - [Products](#) - [Technical Data](#) - [Reps/Distr.](#) - [Contact Us](#)

HIGH DENSITY - CRIMP CONNECTORS - DC3 SERIES

SPECIFICATIONS:

MECHANICAL:

Shell: steel

Finish: tin plated

Insulator: glass filled PBT UL94V0

ELECTRICAL:

Current Rating: 3 amps max.

Voltage Rating: 250 vac

Insulation Resistance: 3000 meg ohm min @ 500 vdc

Contact Resistance: <15 milli ohms (mated)

Temperature Range: -55° TO +105° C

Available Sizes:

Male: 15, 26, 44, 62, & 78 position


Female: 15, 26, 44, 62, & 78 position

[RoHS Compliant](#)

[DOWNLOAD](#)

[DRAWING](#)

[CERTIFICATE OF COMPLIANCE](#)







Part Numbers

XDC3E15PTE	XDC3E15ST	XDC3E26PTE	XDC3E26ST
XDC3E44PTE	XDC3E44ST	XDC3E62PTE	XDC3E62ST
XDC3E78PTE	XDC3E78ST		

[Click here for Non-RoHS Compliant Product Part Number Page](#)

HIGH DENSITY CRIMP CONNECTORS - DC3 SERIES



SIZES 15 TO 62

SPECIFICATIONS:

MECHANICAL

Shell: Steel
Finish: Tin Plate.
Insulator: Thermoplastic UL94V-0.
Temperature Range: -55° to +105° C.
Contacts: See Page 30

Pins	Row Arrangement			
	1st	2nd	3rd	4th
15	5	5	5	-
26	9	9	8	-
44	15	15	14	-
62	21	21	20	-
78	20	19	20	19

ELECTRICAL

Voltage Rating: 300 VDC.
Current Rating: 3 Amps.
IR: > 3000 Meg OHms.
CR: < 15 Milliohms.

CRIMP CONNECTORS - DC3 SERIES - DIMENSIONS

INCHES [MM]

No. of Contacts	Shell Size	A	B	C	D	E Max. Female	F Min. Male	G	H
		±0.005 [±0.127]	±0.005 [±0.127]	±0.005 [±0.127]	±0.005 [±0.127]	±0.005 [±0.127]	±0.005 [±0.127]	±0.005 [±0.127]	±0.005 [±0.127]
15	E (9)	1.213 [30.81]	0.984 [24.99]	0.494 [12.55]	0.759 [19.28]	0.643 [16.33]	0.666 [16.92]	0.422 [10.72]	0.090 [2.29]
26	A (15)	1.541 [39.14]	1.310 [33.27]	0.494 [12.55]	1.089 [27.65]	0.971 [24.66]	0.994 [25.25]	0.422 [10.72]	0.090 [2.29]
44	B (25)	2.088 [53.04]	1.850 [46.99]	0.494 [12.55]	1.626 [41.30]	1.511 [38.38]	1.534 [38.96]	0.422 [10.72]	0.090 [2.29]
62	C (37)	2.730 [69.34]	2.500 [63.50]	0.494 [12.55]	2.261 [57.44]	2.159 [54.84]	2.182 [55.42]	0.422 [10.72]	0.090 [2.29]
78	D (50)	2.638 [67.00]	2.406 [61.11]	0.605 [15.37]	2.178 [55.32]	2.064 [52.43]	2.079 [52.81]	0.533 [13.54]	0.095 [2.41]

ORDER INFORMATION


DC3E 15 P TE

SERIES NAME _____

No OF CONTACTS _____

P: MALE
S: FEMALE

TE: Tin Plate Shell w/ Ground Indents(Male Only)
T: Tin Plate / No Indents (Female)
EMPTY: Yellow Zinc - Consult Factory



78 POSITION