



## Search Results

### Evaluate

- FAQ's

### Design a Solution

- Part Drawings

- PDF-Next Generat ...

### How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor

## Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'UTP6A25BU'

Your search criteria matched only one product, shown below

## UTP6A25BU



- Exceed requirements of ANSI/TIA-568-C.2 Category 6A, IEEE 802.3an-2006, and ISO 11801 Class E<sub>A</sub> channel standards
- Meet requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Each patch cord is 100% performance tested and wired to T568B
- Constructed of TX6A™ 10Gig™ 24 AWG stranded copper cable (nominal cable diameter is 0.280 inches) and TX6™ PLUS Modular Plugs for superior performance
- Plug meets all applicable ANSI/TIA-968-A requirements and exceeds IEC 60603-7 specifications
- Slender strain relief boot provides easy access in high density applications
- Plug uses an integral pair manager to optimize performance and consistency by reducing untwisting of conductors within the plug
- Plug performance in center of TIA/EIA component range, ensuring interoperability and 10GBASE-T Ethernet channel performance
- Labels on patch cords provide identification of performance level, length, and quality control

### number

- Patented tangle free latch prevents snags and provides easy release, saving time on frequent moves, adds, and changes
- Optional Patch Cord Color Bands snap on and off individual patch cables offering endless color-coding options

|                                |                                                                               |
|--------------------------------|-------------------------------------------------------------------------------|
| • Part Number                  | UTP6A25BU                                                                     |
| • RoHS Compliancy Status       | Compliant                                                                     |
| • Part Description             | Category 6A, 10 Gb/s UTP patch cord with TX6™ PLUS Modular Plugs on each end. |
| • Product Type                 | Copper Patch Cord                                                             |
| • Color                        | Blue                                                                          |
| • Length (ft.)                 | 25                                                                            |
| • Length (m)                   | 7.62                                                                          |
| • Boot Color                   | Clear                                                                         |
| • Cable Color                  | Blue                                                                          |
| • Cable Type                   | UTP                                                                           |
| • CE Compliant                 | No                                                                            |
| • Connector 1 Type             | RJ45 8(8)                                                                     |
| • Connector 2 Type             | RJ45 8(8)                                                                     |
| • Flammability Rating          | CM                                                                            |
| • No. of Pairs                 | 4                                                                             |
| • Performance Level            | Category 6A                                                                   |
| • Pricing Description          | Copper Patch Cord, Cat 6A, Blue UTP Cable, 25 Feet                            |
| • Termination End 1            | Modular Plug                                                                  |
| • Termination End 2            | Modular Plug                                                                  |
| • Wiring Scheme                | T568B                                                                         |
| • Min. Order UOM               | PC                                                                            |
| • Min. Order Qty.              | 1                                                                             |
| • BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>                                                |
| • Add to Favorite Product List |                                                                               |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.