

► Heatsinks f.cool

► Cases f.case

▼ Connectors f.con

► Sockets

▼ PCB connectors

■ Male headers

■ Female headers

■ Direct female connector

■ Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

Male headers

SL LP 3 069 14 G

Low profile, angled, square 0.635 mm

add to request



Features

Technical Drawing

Kontaktmaterial	CuSn-Legierung
Oberfläche Kontakt /	Ni+0,2µm Au
Kontakthülse	Ni+4...6µm Sn
surface of contact	gold-plated
no. of contacts	14
volume resistivity	≤5 mΩ
Nennstrom	3 A
nominal voltage	250 V AC
test voltage	2000 V
Material Isolierkörper	PA 4.6, GF
temperature range	-40 °C ... +163 °C (260 °C / 10 s)
class of flammability	UL 94 V-0
insulation resistance	>10 ¹² Ω
connection type	soldering
version	low profile
reflow solderable	yes