

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19154-0030

Status:

Active

Overview:

Splices

Description:

InsulKrimp™ Butt Splice for 10-12 AWG Wire, Tape and Reel



Series

image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-19902-007 \(PDF\)](#)
- [Product Specification PS-19902-011 \(PDF\)](#)
- [Product Specification PS-19902-015 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Splices

Series

19154

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

Splices

Product Name

Butt, InsulKrimp™

UPC

800753108967

Physical

Barrel Type

Closed

Color - Resin

Yellow

Flammability

94V-0

Insulation

PVC

Material - Metal

Copper

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

PVC

Net Weight

2.387/g

Packaging Type

Adhesive Tape on Reel

Wire Size AWG

10, 12

Material Info

Old Part Number

C-246XT

Reference - Drawing Numbers

Product Specification

PS-19902-007, PS-19902-011, PS-19902-015

Sales Drawing

SD-19154-006

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

19154Series

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description	Product #
Mini-Mac™	0638851500
Applicator	
Crimp Dies for	0192880179
MTA-100 Tape	
Applicator used in	
3BF Press, MTA-105	
Tape Applicator used	
in TM-2000™ Press,	
and ATP-301 Air	
Crimping Press for	
Mylar Tape Mounted	
Terminals	

This document was generated on 12/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION