



### Helawrap Cable Cover

- Helawrap HWPP


Helawrap is used to bundle and protect cables in the electrical industry, panel building, machine, automotive and truck manufacturing. Helawrap in 25m lengths is the time-saving solution for industrial applications.

Helawrap in practical 2m lengths is designed for domestic and office use. It puts an end to the cable chaos associated with PCs, TVs and Hi-Fi systems.

#### Features and Benefits

- Ideal solution for bundling, protecting, mounting and routing cables
- Quick and effortless to apply
- Good abrasion protection
- Special profile enables branching off cable at any point
- Can be removed and reapplied often
- Available in several colours and sizes
- Handy applicator tool included

|                              |                                         |
|------------------------------|-----------------------------------------|
| <b>MATERIAL</b>              | Polypropylene (PP)                      |
| <b>Operating Temperature</b> | -60 °C to +110 °C, intermittent +140 °C |
| <b>Flammability</b>          | UL94 HB                                 |



Complete cable management for home and office.



Helawrap, the fast and easy solution to your cable chaos, available in 2 sizes and 3 colours!



Insert one or more cables into the insertion slot of the applicator tool.



Place the applicator tool in one end of the Helawrap cable cover.



Simply slide the applicator tool through the Helawrap cover.

**Helawrap made of flame-retardant polyamide 6 can be found in the Engineered Solutions Catalogue.**



One Step to the Web!



## Helawrap Cable Cover

### • Helawrap HWPP

| TYPE   | Bundle<br>Ø max. | Colour      | Reel<br>Length | Application<br>Tool | Article-No. |
|--------|------------------|-------------|----------------|---------------------|-------------|
| HWPP8  | 9                | Black (BK)  | 25 m           | HAT8                | 161-64101   |
|        | 9                | Grey (GY)   | 25 m           | HAT8                | 161-64102   |
|        | 9                | Silver (SR) | 25 m           | HAT8                | 161-64103   |
|        | 9                | White (WH)  | 25 m           | HAT8                | 161-64104   |
| HWPP16 | 16               | Black (BK)  | 25 m           | HAT16               | 161-64201   |
|        | 16               | Grey (GY)   | 25 m           | HAT16               | 161-64202   |
|        | 16               | Silver (SR) | 25 m           | HAT16               | 161-64203   |
|        | 16               | White (WH)  | 25 m           | HAT16               | 161-64207   |
| HWPP20 | 21               | Black (BK)  | 25 m           | HAT20               | 161-64301   |
|        | 21               | Grey (GY)   | 25 m           | HAT20               | 161-64302   |
|        | 21               | Silver (SR) | 25 m           | HAT20               | 161-64303   |
|        | 21               | White (WH)  | 25 m           | HAT20               | 161-64304   |
| HWPP25 | 27               | Black (BK)  | 25 m           | HAT25               | 161-64401   |
|        | 27               | Grey (GY)   | 25 m           | HAT25               | 161-64402   |
|        | 27               | Silver (SR) | 25 m           | HAT25               | 161-64403   |
|        | 27               | White (WH)  | 25 m           | HAT25               | 161-64407   |
| HWPP30 | 32               | Black (BK)  | 25 m           | HAT30               | 161-64501   |
|        | 32               | Grey (GY)   | 25 m           | HAT30               | 161-64502   |
|        | 32               | Silver (SR) | 25 m           | HAT30               | 161-64503   |
|        | 32               | White (WH)  | 25 m           | HAT30               | 161-64504   |

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.

| TYPE     | Bundle<br>Ø max. | Colour      | Length<br>(L) | Application<br>Tool | Article-No. |
|----------|------------------|-------------|---------------|---------------------|-------------|
| HWPP16L2 | 16               | Black (BK)  | 2 m           | HAT16               | 161-64204   |
|          | 16               | Grey (GY)   | 2 m           | HAT16               | 161-64205   |
|          | 16               | Silver (SR) | 2 m           | HAT16               | 161-64206   |
| HWPP25L2 | 27               | Black (BK)  | 2 m           | HAT25               | 161-64404   |
|          | 27               | Grey (GY)   | 2 m           | HAT25               | 161-64405   |
|          | 27               | Silver (SR) | 2 m           | HAT25               | 161-64406   |

All dimensions in mm. Subject to technical changes.

Minimum Order Quantity (MOQ) may differ from package content.