




★★★★★ Five Star 7000 Series Medium Head Cutters

Made in the USA

Edge hardened to 63/65 Rockwell "C"

Stainless Steel Leaf Springs – Angulated Head for Cutting in Dense Areas

7100 Series Medium Head Cutters with Long Foam Cushion Grips

★★★★★ 5 3/4" Medium Round Head Cutters

7140E	Semi-Flush Cut				
	Cutting Capacity	.008"	–	.042"	
7141E	Maximum Flush Cut				
	Cutting Capacity	.005"	–	.040"	
7142E	Optimum Flush Cut				
	Cutting Capacity	.003"	–	.032"	
A	B	C	D	E	F
.440"	.275"	.430"	N/A	N/A	16°



7200 Series Medium Head Cutters with Ergonomic Molded Grips

★★★★★ 5" Medium Round Head Cutters

7240E	Semi-Flush Cut				
	Cutting Capacity				.008" – .042"
7241E	Maximum Flush Cut				
	Cutting Capacity				.005" – .040"
7242E	Optimum Flush Cut				
	Cutting Capacity				.003" – .032"
A	B	C	D	E	F
.440"	.275"	.430"	N/A	N/A	16°



★★★★★ 5 3/4" Medium Tapered Head Cutters

7143E	Semi-Flush Cut				
	Cutting Capacity				.008" – .036"
7144E	Maximum Flush Cut				
	Cutting Capacity				.005" – .036"
7145E	Optimum Flush Cut				
	Cutting Capacity				.002" – .028"
A	B	C	D	E	F
.440"	.275"	.430"	.050"	N/A	16°



★★★★★ 5" Medium Tapered Head Cutters

7243E	Semi-Flush Cut				
	Cutting Capacity	.008" – .036"			
7244E	Maximum Flush Cut				
	Cutting Capacity	.005" – .036"			
7245E	Optimum Flush Cut				
	Cutting Capacity	.002" – .028"			
A	B	C	D	E	F
.440"	.275"	.430"	.050"	N/A	16°



★★★★★ 5 3/4" Medium Tapered/Relieved Cutters

7146E	Semi-Flush Cut				
	Cutting Capacity	.008" – .036"			
7147E	Maximum Flush Cut				
	Cutting Capacity	.005" – .036"			
7148E	Optimum Flush Cut				
	Cutting Capacity	.002" – .028"			
A	B	C	D	E	F
.440"	.275"	.430"	.050"	N/A	16°



★★★★★ 5" Medium Tapered/Relieved Cutters

7246E	Semi-Flush Cut				
	Cutting Capacity		.008" – .036"		
7247E	Maximum Flush Cut				
	Cutting Capacity		.005" – .036"		
7248E	Optimum Flush Cut				
	Cutting Capacity		.002" – .028"		
A	B	C	D	E	F
.440"	.275"	.430"	.050"	N/A	16°

