




THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER
ORIGINAL (1)



ALLOW TO HAVE EXTRAS CAVITIES
ON THIS SURFACE FOR SHRINKING
PURPOSE AS PER MOLDER REQUEST



MATERIALS AND FINISH

1: STEEL, NICKEL PLATED

2: INSULATOR, NYLON 6T, COLOR PANTONE BLUE #2935U

3: CONTACTS: PHOSPHOR BRONZE, GOLD PLATED ON CONTACT AREA
TIN ON TAILS OVER NICKEL

4: BOARD LOCKS, BRASS TIN PLATED

5: RIVETS, BRASS NICKEL PLATED

SPECIFICATIONS

CURRENT RATING: 1 AMP MAX.

INSULATION RESISTANCE: 1000 MEGOHMS MIN. AT 500 VDC

DWD: 500 VAC rms FOR 1 MINUTE

CONTACT RESISTANCE: 30 MILLOHMS MAX.

TEMPERATURE RATING: -40°C +230°C

MAX. PROCESSED TEMPERATURE: +265°C FOR 10 SEC. AND
+230°C FOR 60 SEC.

CONTACT POSITION 9th RECESSED

634 SERIES HDD SUBMINIATURE CONNECTOR
15 CONTACTS RECEPTACLE(SOCKET) RIGHT ANGLE ULTRA SLIM
WITH TRIPLE-BEAM BOARDLOCK



THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANT.



EDAC INC
TORONTO, ONTARIO
CANADA
YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC. AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

DRAWN: R.BLAKEY	DATE: March 8/07
CHECKED:	DATE:
PART NUMBER	
634-015-274-992	
DRAWING NUMBER	ISSUE
634-015-274-992	3