




Optrex America, Inc

PART NO : MG 780F-LY

DWG NO : DW03075

ANGLE PROJ. :

REV : 0

SIGNATURE

PROJECT : 780

DWG DATE : 30 JUN 08

UNIT: mm

SCALE : 2 : 1

ORIGINATOR: WANG HUA


TITLE : MODULE (120 X 32 DOTS)

UNIT: mm

SHEET 1 OF 2

CHECK BY:

PCB IC SIDE



PIN ASSIGNMENT

Pin No.	Symbol	Pin No.	Symbol
01	GND	10	DB0
02	GND	11	DB1
03	V _{cc}	12	DB2
04	V _{EE}	13	DB3
05	RS	14	DB4
06	R/W	15	DB5
07	/CS1	16	DB6
08	/CS2	17	DB7
09	V _{cc}	18	V _{cc}

DISPLAY FORMAT :	120 X 32 DOTS
VIEWING DIRECTION:	6:00 O'CLOCK
MODE:	POSITIVE
DISPLAY TYPE:	FSTN, TRANSMISSIVE
MULTIPLEX RATIO:	1/32
IC:	EPSON SED1530DAA
LED BACK LIGHT COLOR:	YELLOW-GREEN
OPERATING TEMP:	0 °C TO 70 °C
STORAGE TEMP:	0 °C TO 70 °C

Optrex America, Inc

PART NO : MG 780F-LY

DWG NO : DW03075

ANGLE PROJ. :

REV : 0

SIGNATURE

PROJECT : 780

DWG DATE : 30 JUN 08

SCALE : 2 : 1

ORIGINATOR: WANG HUA

TITLE : MODULE (120 X 32 DOTS)

UNIT: mm

SHEET 2 OF 2

CHECK BY: