











SCALE 3:2

SCALE 3:2

1) MATED WITH SOCKET HOUSING P/N 953122-6
(DIMA ADATTA A CONTROPARTE P/N 953122-6)

P/N 1745060-1 AS SHOWN
(COME MOSTRATO)

I745060-I	6	10	PIN □0.63	Cu ALLOY (LEGA DI RAME)	Sn PRETINNED (STAGNATO)
	5	10	PIN □0.63	Cu ALLOY (LEGA DI RAME)	Sn PRETINNED (STAGNATO)
	4	10	PIN □0.63	Cu ALLOY (LEGA DI RAME)	Sn PRETINNED (STAGNATO)
	3	10	PIN □0.63	Cu ALLOY (LEGA DI RAME)	Sn PRETINNED (STAGNATO)
	2	1	CENTER PLATE 40 POS. (POSIZIONATORE CONTATTI)	PA6/6-GF	BLACK (NERO)
	1	1	PIN HEADER 40 POS. (DIMA 40 VIE)	PBT-GF	GREY (GRIGIO)
P/N	ITEM (COMP.)	Q.TY (Q.TA)	DESCRIPTION (DESCRIZIONE)	MATERIAL (MATERIALE)	SURFACE/COLOR FINITURA/COLORE

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 15JUN2005 F. AMERIO		tyco Electronics		Tyco Electronics AMP Italy C.so F.lli Cervi 15 Collegno (To)	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHR 15JUN2005 O. CANUTO		NAME	
		APVD 15JUN2005 A. GENTA		PIN HEADER 40 POS. MQS			
		PRODUCT SPEC -		SIZE CAGE CODE DRAWING NO RESTRICTED			
		APPLICATION SPEC -		A2 00779 G-1745060		-	
		ANGLES FINISH ±-		WEIGHT -		-	
MATERIAL SEE TABLE		CUSTOMER DRAWING		SCALE 1 : 1 SHEET OF REV A			