



Drills - Percussion Drills - 770 W - Percussion Drill with keyless chuck & kitbox
D21805KS



D21805KS Features

- Two speed gearbox for increased torque
- Improved drilling performance due to new motor wind
- Improved ergonomics with new polymer gear case
- New gear design to give improved life
- Improved unit life with patented armature support

D21805KS Specifications

Chuck Capacity	1.5-13 mm
Power Input	770 Watts
Power Output	425 Watts
Max Torque	40/20 Nm
No Load Speed	0-1100 / 0-2700 rpm
Blows per Minute	0-18700 / 0-45900 bpm
Max. Drilling Capacity [Wood]	35 mm
Max. Drilling Capacity [Steel]	13 mm
Max. Drilling Capacity [Concrete]	20 mm
Spindle Thread	1/2" X 20 U.N.F
Weight	2.3 kg
Length	352 mm
Height	199 mm

D21805KS Standard

- Multi-position side handle
- Depth stop
- Heavy duty carrying case
- Keyless chuck