

Single-Phase Basic PDU, 2.4kW 20A 120V, 0U Vertical Rackmount, 14 NEMA 5-15/20R outlets, NEMA L5-20P input plug

MODEL NUMBER: **PDU1420T**



Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 20A single phase 120V Basic Power Distribution Unit / PDU
- Attached NEMA L5-20P 20A 120V input plug with 15 ft. / 4.5m line cord
- 0U, 24 in. / 61cm vertical form factor supports installation in 2 or 4 post equipment racks
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications

Specifications

OVERVIEW	
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
PDU Type	Basic
OUTPUT	
Output Capacity Details	2.4kW (120V input), 2.5kW (127V input), 2.0kW (100V input); 20A maximum
Frequency Compatibility	50 / 60 Hz
Output (Watts)	2400
Output Nominal Voltage	100-127V nominal, single phase

Highlights

- Basic single phase 20A 120V PDU
- 0U vertical rackmount installation
- NEMA L5-20P locking input; 15 ft. / 4.5m line cord
- 14 NEMA 5-15/20R outlets
- 24 in. / 61cm height

Applications

- Multi-outlet power distribution unit is the ideal means of powering multiple loads in racks, wallmount and other applications, such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Package Includes

- PDU1420T power strip
- Instruction manual with warranty information

Overload Protection	20A
Outlet Quantity / Type	14 NEMA 5-15/20R
Number of Outlets	14
Outlet Type	NEMA 5-15R, NEMA 5-20R
INPUT	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	20
PDU Plug Type	NEMA L5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	No switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.75 x 27.25 x 8.25
Shipping Dimensions (hwd / cm)	7 x 69.2 x 21
Shipping Weight (lbs.)	6.2
Shipping Weight (kg)	2.8
Unit Dimensions (hwd / in.)	1.75 x 24 x 2.25
Unit Dimensions (hwd / cm)	4.45 x 61 x 5.7
Unit Weight (lbs.)	5.6
Unit Weight (kg)	2.5
Material of Construction	Steel
Form Factors Supported	Vertical or horizontal mounting supported in wallmount applications, racks and a variety of other surface types
PDU Form Factor	Vertical (0U)
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com