



Combination spanner, offset, 111M

Combination spanners, offset in Metric sizes.

DIN 3113 / ISO 3318 / ISO 7738

Finish: nickel and chrome-plated, fine-polished.

Material: VANADIUM-EXTRA.

Open-end angle 15°, ring end 15° offset, equal openings at both ends, short type.

With Dynamic-Drive-Profile.

SB = Retail packed on a plastic info card.



				L mm	a1xa2 mm	b1xb2 mm	
111M-5.5	1828608	10	5.5	105	5.0x3.2	9.5x14	12
111M-6	1828615	10	6	105	5.0x3.2	10.0x14	13
111M-7	1828622	10	7	110	5.6x3.5	11.0x17	18
111M-8	1828639	10	8	110	5.6x3.5	12.0x18	18
111M-9	1828646	10	9	120	6.0x3.8	13.8x20	22
111M-10	1828653	10	10	135	6.6x4.2	15.0x22	30
111M-11	1828660	10	11	135	6.6x4.2	16.5x23	30
111M-12	1828677	10	12	150	7.4x4.7	18.0x26	45
111M-13	1828684	10	13	160	7.4x4.7	19.5x28	45
111M-14	1828691	10	14	168	8.2x5.3	20.6x31	65
111M-15	1828707	10	15	170	8.2x5.3	22.0x32	65
111M-16	1828714	10	16	178	8.8x5.6	23.4x34	80
111M-17	1828721	10	17	190	9.4x6.0	24.8x37	110
111M-18	1828738	10	18	210	10.0x6.3	26.4x39	115
111M-19	1828745	10	19	220	10.0x6.3	27.6x40	120
111M-20	1828752	10	20	232	11.0x7.0	29.0x42	150
111M-21	1828769	10	21	250	11.0x7.0	30.4x44	150
111M-22	1828776	5	22	255	12.0x7.7	31.8x48	200
111M-23	1828783	5	23	255	12.0x7.7	33.4x48	210
111M-24	1828790	5	24	280	13.0x8.4	34.6x50	265
111M-25	1828806	5	25	280	13.0x8.4	36.0x51	270
111M-26	1828813	5	26	280	13.0x8.4	37.5x53	270
111M-27	1828820	5	27	310	14.0x9.2	38.8x57	350
111M-28	1828837	5	28	310	14.0x9.2	40.5x58	365
111M-29	1828844	5	29	310	14.0x9.2	41.0x58	380
111M-30	1828851	5	30	355	15.0x10.0	43.5x62	480
111M-32	1828868	5	32	360	15.0x10.0	46.0x65	500
111M-34	1828875	5	34	380	15.0x10.0	47.0x65	500
SB111M-5,5	1839819	1	5.5	105	5.0x3.2	9.5x14	22
SB111M-6	1839826	1	6	105	5.0x3.2	10.0x14	23
SB111M-7	1839833	1	7	110	5.6x3.5	11.0x17	28
SB111M-8	1839840	1	8	110	5.6x3.5	12.0x18	28
SB111M-9	1839857	1	9	120	6.0x3.8	13.8x20	32
SB111M-10	1839864	1	10	135	6.6x4.2	15.0x22	40
SB111M-11	1839871	1	11	135	6.6x4.2	16.5x23	40
SB111M-12	1839888	1	12	150	7.4x4.7	18.0x26	55
SB111M-13	1839895	1	13	160	7.4x4.7	19.5x28	55
SB111M-14	1839901	1	14	168	8.2x5.3	20.6x31	75

Bahco Group - Product Card

SB111M-15	1839918		15	170	8.2x5.3	22.0x32 75
SB111M-16	1839925	1	16	178	8.8x5.6	23.4x34 90
SB111M-17	1839932	1	17	190	9.4x6.0	24.8x37 120
SB111M-18	1839949	1	18	210	10.0x6.3	26.4x39 125
SB111M-19	1839956	1	19	220	10.0x6.3	27.6x40 130
SB111M-20	1839963	1	20	232	11.0x7.0	29.0x42 160
SB111M-21	1839970	1	21	250	11.0x7.0	30.4x44 160
SB111M-22	1839987	1	22	255	12.0x7.7	31.8x48 210
SB111M-23	1839994	1	23	255	12.0x7.7	33.4x48 220
SB111M-24	1840006	1	24	280	13.0x8.4	34.6x50 275
SB111M-25	1840013	1	25	280	13.0x8.4	36.0x51 280
SB111M-26	1840020	1	26	280	13.0x8.4	37.5x53 280
SB111M-27	1840037	1	27	310	14.0x9.2	38.8x57 360
SB111M-28	1840044	1	28	310	14.0x9.2	40.5x58 375
SB111M-29	1840051	1	29	310	14.0x9.2	41.0x58 390
SB111M-30	1840068	1	30	355	15.0x10.0	43.5x62 490
SB111M-32	1840075	1	32	360	15.0x10.0	46.0x65 510
SB111M-34	0105175	1	34	380	15.0x10.0	47.0x65 500