




FEATURES:

- Accepts standard banana plugs
- Mounts in panels from 1.57 (.062) to 6.35 (.250) thick.

MATERIALS:

Insulated Captive Thumb Nut: Brass

Finish: Nickel plated brass

Insulation: Polycarbonate

Mounting Base: Polycarbonate

Insulator: Polycarbonate

Lockwasher: Steel

Hex Nut: Brass

Binding Post: Nickel plated brass;

Terminal: Gold Plated phosphor bronze

RATINGS:

Voltage: Hand-held testing: 30VAC/60VDC Max.

Hands free testing in controlled voltage environments: 2500 WVDC Max.

Operating Temperature: +115°C (+239°F) Max.

Current: 3 Amperes

ORDERING INFORMATION: Model 4098-*

*=Color, -0 Black, -2 Red

Ordering Example: 4098-2 Color is Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4098-0](#) [4098-2](#)