

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190950028

Status:

Active

Description:

Terminal Lugs for 22-18 AWG, Insulated Red Sleeve, Stud Size 5 (M3), Length 21.82mm (.859")

Documents:

Drawing (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Comments

Crimp Quality Equipment

Mil-Spec

Product Name

Type

Ring and Spade Terminals

19095

Type II Insulated; Class 1 and 2

Yes

AS17143-10, MS17143-10

Avikrimp™

Ring

Physical

Barrel Type

Insulation

Material - Plating Mating

Packaging Type

Plating min - Mating

Plating min - Termination

Stud Size

Wire Size AWG

Closed

Nylon (PA)

Tin

Bag

2.540µm (100µ")

2.540µm (100µ")

5 (M3)

18, 20, 22

Material Info

Old Part Number

AA-883-1

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011, PS-19902-013

SD-19095-006

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19095Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool

0640010100

Crimp Head for the

0640050100

AT-200™ Pneumatic

Hand Tool

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19095-0028](#)