

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0543932381](#)
Status: **Active**
Description: 0.30mm (.012") Pitch Easy-On™ Type, Right Angle, SMT, ZIF, Bottom Contact, 23 Circuits, Lead-Free, Gold (Au) Contact Plating

Documents:

[3D Model](#) [Product Specification PS-54393-064 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
Series [54393](#)
Product Name Easy-On™

Physical

Circuits (Loaded) 23
Contact Position Bottom
Durability (mating cycles max) 20
Entry Angle 90° Angle
Mated Height 1.95mm (.077")
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Gold
Number of Rows 1
Orientation Right Angle
PCB Locator No
PCB Retention Yes
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 0.30mm (.012")
Polarized to PCB Yes
Stackable No
Temperature Range - Operating -20°C to +85°C
Termination Interface: Style Surface Mount
Wire/Cable Type FPC only

Electrical

Current - Maximum per Contact 0.2A
Voltage - Maximum 50V

Material Info

Reference - Drawing Numbers

Product Specification PS-54393-064, RPS-54393-079, RPS-54393-080,
RPS-54393-081, RPS-54393-082
Sales Drawing SD-54393-023, SD-54393-024




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[54393Series](#)