



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .020$	W $\pm .010$	C $\pm .015$	M $\pm .020$	H $\pm .010$
P10-10FF	#10	.80 (20.32)	.38 (9.65)	.28 (7.11)	.55 (13.97)	.20 (5.08)

NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. #12-10 AWG SOLID OR STRANDED COPPER WIRE
 - B. 347° F (175° C) MAX. TEMP. RATING
2. MATERIAL:
 - A. STAMPING - .04" (1.12) THK COPPER, TIN PLATED
3. PACKAGE QTY: STD. PKG. 50
 BULK PKG. 500
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOLS: CT-100, CT-160, CT-200



LISTED
587H
E52164



CERTIFIED
LR31212

A41238_04

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
04	2/01	KMD		DRAWING NUMBER WAS A41238A				#12-10 BARREL NON-INSULATED FLANGED FORK			
03	7-88	DW		REDRAWN WITH REVISIONS	07629						
REV	DATE	BY	CHK	DESCRIPTION	ECN	PM	APP	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								DAW		NONE	A41238